



Specification



- Lever body
Zinc die-cast
- Powder coated
 - Black, RAL 9005, textured finish ● **SW**
 - Orange, RAL 2004, textured finish ● **OS**
 - Red, RAL 3000, textured finish ● **RS**
 - Silver, RAL 9006, textured finish ● **SR**
- Threaded stud / retaining screw
Steel, zinc plated, blue passivated finish
- RoHS compliant

Information

GN 302.2 adjustable levers have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.

These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

see also...

- *Straight Adjustable Levers GN 302 (Steel Threaded Stud, Blackened Finish)* → page QVX
- *Straight Adjustable Levers GN 302.1 (Stainless Steel Threaded Stud)* → page QVX
- *Adjustable Levers GN 300.2 (Steel Threaded Stud, Zinc Plated)* → page QVX

How to order (Inch)	1 Lever length l_1
GN 302.2-45-1/4X20-10-SW	2 Thread d_1
	3 Thread length l_2
	4 Color

How to order (Metric)	1 Lever length l_1
GN 302.2-78-M8-25-RS	2 Thread d_1
	3 Thread length l_2
	4 Color

Inch table

Dimensions in: inches - *millimeters*

1	2	3									d₃	d₄	h₁	h₂	h₃	h₄ Stroke	
l₁	d₁	l₂															
1.77 45	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	
1.77 45	10 x 24	0.63 16	0.79 20	1.26 32	-	-	-	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	
1.77 45	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5	
2.48 63	1/4 x 20	0.63 16	0.79 20	0.98 25	-	-	-	-	-	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4	
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4	
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	-	0.63 16	0.83 21	1.42 36	0.31 8	1.34 34	0.16 4	
3.07 78	1/2 x 13	1.26 32	1.57 40	-	-	-	-	-	-	-	0.63 16	0.83 21	1.42 36	0.31 8	1.34 34	0.16 4	

Metric table

Dimensions in: millimeters - *inches*

1	2	3									d₃	d₄	h₁	h₂	h₃	h₄ Stroke	
l₁	d₁	l₂															
22 0.87	M 3	-	6 0.24	8 0.31	10 0.39	12 0.47	16 0.63	-	-	-	8 0.31	10.5 0.41	18.5 0.73	2 0.08	16.5 0.65	3 0.12	
22 0.87	M 4	M 5	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	8 0.31	10.5 0.41	18.5 0.73	2 0.08	16.5 0.65	3 0.12	
30 1.18	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	
30 1.18	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	
45 1.77	M 4	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	
45 1.77	M 5	M 6	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14	
63 2.48	M 6	M 8	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	2.48	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	28.5 1.12	4 0.16	
78 3.07	M 8	M 10	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	2.48	16 0.63	21 0.83	36 1.42	8 0.31	34 1.34	4 0.16	