



Inch | Metric



Inch table

1 2

Dimensions in: inches / millimeters

l_1	d_1			d_2	d_3	h_1	h_2	h_3	h_4 Stroke	t min.
1.77 45	10 x 32	10 x 24	1/4 x 20	0.39 10	0.51 13	1.04 26.5	0.16 4	1.38 35	0.14 3.5	0.35 9
2.48 63	1/4 x 20	5/16 x 18	-	0.53 13.5	0.69 17.5	1.28 32.5	0.26 6.5	1.77 45	0.16 4	0.43 11
3.07 78	5/16 x 18	3/8 x 16	-	0.63 16	0.83 21	1.48 37.5	0.31 8	2.17 55	0.16 4	0.55 14

Metric table

1 2

Dimensions in: millimeters / inches

l_1	d_1			d_2	d_3	h_1	h_2	h_3	h_4 Stroke	t min.
30 1.18	M 4	M 5	M 6	10 0.39	13 0.51	26.5 1.04	4 0.16	31 1.22	3.5 0.14	9 0.35
45 1.77	M 4	M 5	M 6	10 0.39	13 0.51	26.5 1.04	4 0.16	35 1.38	3.5 0.14	9 0.35
63 2.48	M 6	M 8	-	13.5 0.53	17.5 0.69	32.5 1.28	6.5 0.26	45 1.77	4 0.16	11 0.43
78 3.07	M 8	M 10	-	16 0.63	21 0.83	37.5 1.48	8 0.31	55 2.17	4 0.16	14 0.55

Specification

Lever body

Zinc die-cast
Powder coated
Black, RAL 9005, textured finish ● SW

Tapped insert

Steel, zinc plated, blue passivated finish

Push button

Plastic, Polyamide (PA)
• Black, RAL 9005 ● S
• Orange, RAL 2004 ● O
• Gray, RAL 7035 ● G

RoHS

On request

• Lever body in GN 300 colors

Adjustable levers GN 303.2 with push button have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.

The push button is a design element and allows for effortless release action. However, this design is limited to applications that do not require the lever to be disassembled.

How to order (Inch)

1 2 3 4
GN 303.2-45-10X32-SW-O

- 1 Lever length l_1
- 2 Thread d_1
- 3 Lever color
- 4 Push button color

How to order (Metric)

1 2 3 4
GN 303.2-78-M10-SW-G

- 1 Lever length l_1
- 2 Thread d_1
- 3 Lever color
- 4 Push button color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4