


Inch | Metric



3 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side (only for $d_1 = 28$ mm)

Specification

Handle tube

- Aluminum, wall thickness 1.5 mm
- Powder coated
 - Black, RAL 9005, textured finish
 - Handle legs black
- Anodized finish, natural color
 - Handle legs black
- Anodized finish, natural color
 - Handle legs silver

- **SW**
- **EL**
- **ES**

Handle legs

- Zinc die-cast
- Powder coated, textured finish
- Black, RAL 9005 for SW / EL
- Silver, RAL 9006 for ES

Cover

- Plastic, light gray

Mounting set (Type B)

- Socket button head screws ISO 7380-M6-20
 - Steel, zinc plated
 - Black passivated finish for SW / EL
 - Blue passivated finish for ES
- Hex nuts ISO 4032-M6
 - Steel, zinc plated, blue passivated finish
- Washers DIN 125
 - Steel, zinc plated, blue passivated finish

RoHS

The handle tube of the tubular handles GN 333.1 can be screwed to the handle bases without further machining or processing, allowing special lengths to be realised easily.

Further handle legs can be added for very long tubular handles. Individual handle legs for tubular handles $\varnothing 28$ (type A) are available under GN 333.9. For type B, socket button head screws, hex nuts and washers are included.

see also...

	Page
GN 333 Tubular Handles (with Angled Handle Legs)	QVX
GN 333.7 Tubular Handles (Stainless Steel)	QVX
GN 331 Tubular Handles (with Power Switching Function)	QVX

Technical Information

Load Capacity Information	QVX
---------------------------	-----

Accessory

GN 333.9 Straight Handle Legs (for Tubular Handles $\varnothing 28$ mm)	QVX
--	-----

How to order (Inch)

GN 333.1-0.79-12.00-A-ES

1	Handle diameter d_1
2	Length l_1
3	Type
4	Finish

How to order (Metric)

GN 333.1-28-400-B-SW

1	Handle diameter d_1
2	Length l_1
3	Type
4	Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4



Inch table



Dimensions in: inches / millimeters

d₁	l₁							d₂	b₁	b₂	h₁	h₂	t min.
0.79 20.1	7.00 177.8	8.00 203.2	10.00 254	12.00 304.8	16.00 406.4	-		1/4 x 20	0.94 23.9	0.47 11.9	1.97 50	2.60 66	0.59 15
1.10 27.9	8.00 203.2	10.00 254	12.00 304.8	16.00 406.4	20.00 508	24.00 609.6		5/16 x 18	0.98 24.9	0.98 24.9	1.97 50	2.60 66	0.59 15

Metric table



Dimensions in: millimeters / inches

d₁	l₁							d₂	d₃	b₁	b₂	h₁	h₂	h₃	l₂ max.	l₃	t min.
20 0.79	180 7.09	200 7.87	250 9.84	300 11.81	350 13.78	400 15.75	-	M 6	-	24 0.94	12 0.47	42 1.65	54 2.13	-	-	-	12 0.47
28 1.10	200 7.87	250 9.84	300 11.81	350 13.78	400 15.75	500 19.69	600 23.62	M 8	M 6	25 0.98	14 0.55	50 1.97	66 2.60	7 0.28	6 0.24	13 0.51	15 0.59
30 1.18	200 7.87	300 11.81	350 13.78	400 15.75	500 19.69	600 23.62	1000 39.37	M 8	-	27 1.06	17 0.67	51 2.01	68 2.68	-	-	-	15 0.59