Straight Adjustable Levers

Zinc Die-Cast, Threaded Stud Type, Steel Components, with Push Button

JW WINCO® A Ganter Company

Inch | Metric





Specification

Lever body
Zinc die-cast
Powder coated

• Black, RAL 9005, textured finish	● SW
• Orange, RAL 2004, textured finish	● OS
• Red, RAL 3000, textured finish	● RS
• Silver, RAL 9006, textured finish	● SR

Threaded stud
Steel, blackened finish

Push button
Plastic

• Black, RAL 9005	● S
• Orange, RAL 2004	● O
• Gray, RAL 7035	● G

RoHS

On request

• Special stud lengths and threads

Adjustable levers GN 304 with push button have a straight lever parallel to the clamping surface. For some applications this presents an advantage due to limits of space or for visual reasons.
These levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.
Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the serrations automatically re-engage.
The push button is a design element and allows for effortless release action. However, this design is limited to applications that do not require the lever to be disassembled.

see also...	Page
GN 302 Straight Adjustable Levers (Zinc Die-Cast, with Blackened Steel Threaded Stud)	QVX
WN 304 Straight Adjustable Levers (Nylon Plastic, with Steel Threaded Stud, with Push Button)	QVX
WN 302 Straight Adjustable Levers (Nylon Plastic, with Blackened Steel Threaded Stud Type)	QVX

How to order (Inch)

GN 304-63-5/16X18-63-OS-G

1	Lever length l_1
2	Thread d_1
3	Thread length l_2
4	Lever color
5	Push button color

How to order (Metric)

GN 304-45-M5-25-RS-S

1	Lever length l_1
2	Thread d_1
3	Thread length l_2
4	Lever color
5	Push button color

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

Inch table

Dimensions in: inches / millimeters

l_1	d_1	l_2								d_3	d_4	h_1	h_2	h_3	h_4 Stroke
1.18 30	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.18 30	10 x 24	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.18 30	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.77 45	10 x 32	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.77 45	10 x 24	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
1.77 45	1/4 x 20	0.39 10	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	-	0.39 10	0.51 13	0.96 24.5	0.16 4	0.87 22	0.14 3.5
2.48 63	1/4 x 20	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	-	-	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4
2.48 63	5/16 x 18	0.47 12	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.97 50	2.48 63	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4
2.48 63	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.97 50	2.48 63	-	0.53 13.5	0.69 17.5	1.22 31	0.26 6.5	1.12 28.5	0.16 4
3.07 78	3/8 x 16	0.63 16	0.79 20	0.98 25	1.26 32	1.57 40	1.77 45	1.97 50	2.48 63	0.63 16	0.83 21	1.42 36	0.31 8	1.34 34	0.16 4

Metric table

Dimensions in: millimeters / inches

l_1	d_1		l_2									d_3	d_4	h_1	h_2	h_3	h_4 Stroke
30 1.18	M 3	-	6 0.24	8 0.31	10 0.39	12 0.47	16 0.63	-	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
30 1.18	M 4	-	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
30 1.18	M 5	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
30 1.18	M 6	-	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	45 1.77	50 1.97	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
45 1.77	M 4	-	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	-	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
45 1.77	M 5	-	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
45 1.77	M 6	-	10 0.39	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	-	10 0.39	13 0.51	24.5 0.96	4 0.16	22 0.87	3.5 0.14
63 2.48	M 6	M 8	12 0.47	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	-	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	28.5 1.12	4 0.16
63 2.48	M 10	-	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	13.5 0.53	17.5 0.69	31 1.22	6.5 0.26	28.5 1.12	4 0.16
78 3.07	M 8	M 10	16 0.63	20 0.79	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	16 0.63	21 0.83	36 1.42	8 0.31	34 1.34	4 0.16
78 3.07	M 12	-	25 0.98	32 1.26	40 1.57	50 1.97	63 2.48	80 3.15	-	-	-	16 0.63	21 0.83	36 1.42	8 0.31	34 1.34	4 0.16