


Metric



**4 Type**

**B** Through hole

**Metric table**

Dimensions in: millimeters / inches

<b>1</b> <b>d<sub>1</sub></b>	<b>2</b> <b>h</b>					<b>3</b> <b>d<sub>2</sub></b>
15 0.59	12 0.47	15 0.59	20 0.79	-	-	6.5 0.26
20 0.79	15 0.59	20 0.79	25 0.98	30 1.18	-	8.5 0.33
25 0.98	15 0.59	20 0.79	25 0.98	30 1.18	40 1.57	10.5 0.41
30 1.18	20 0.79	30 1.18	40 1.57	-	-	13.5 0.53
40 1.57	20 0.79	30 1.18	40 1.57	50 1.97	-	13.5 0.53
50 1.97	30 1.18	40 1.57	50 1.97	-	-	17 0.67
60 2.36	30 1.18	60 2.36	-	-	-	17 0.67
80 3.15	30 1.18	40 1.57	50 1.97	80 3.15	-	21 0.83
100 3.94	30 1.18	40 1.57	80 3.15	-	-	21 0.83

**Specification**

**Rubber**

Natural rubber (NR), black

- Operating temperature  
-40 °F to +176 °F (-40 °C to +80 °C)

- Hardness Shore A ±5

- Soft **40**
- Medium **55**
- Hard **70**

RoHS



Vibration isolation mounts GN 351 are suitable for the elastic mounting of machine units such as motors, compressors and pumps. Fastening can be carried out flexibly, e.g. with standard screws.

**see also...**

**GN 353 | GN 453** Vibration / Shock Absorption Mounts **Page** QVX

**Technical Information**

Overview of Types Vibration Damping Elements / Vibration Isolation Mounts / Rubber Bumpers **QVX**

Technical Instructions Vibration Isolation Mounts / Rubber Bumpers **QVX**

Resilience Characteristics **QVX**

Plastic Characteristics **QVX**

**How to order**

<b>1</b>	<b>Outside diameter d<sub>1</sub></b>
<b>2</b>	<b>Height h</b>
<b>3</b>	<b>Bore diameter d<sub>2</sub></b>
<b>4</b>	<b>Type</b>
<b>5</b>	<b>Hardness</b>

**GN 351-30-20-13.5-B-70**

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

