



SS Stainless Steel

- 3 Type**
- A With threaded spindle
  - B With tapped spindle

**Inch table**

Dimensions in: inches - millimeters

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> ±0.04	l <sub>3</sub> ±0.04	A/F in mm	t min.
0.98 25	1/4 x 20	0.39 10	0.43 11	1.48 37.5	0.59 15	8	0.39 10
1.26 32	5/16 x 18	0.51 13	0.51 13	1.89 48	0.75 19	10	0.47 12
1.57 40	3/8 x 16	0.63 16	0.55 14	2.40 61	0.94 24	14	0.63 16
1.97 50	1/2 x 13	0.79 20	0.83 21	3.07 78	1.22 31	17	0.63 16

**Metric table**

Dimensions in: millimeters - inches

<sup>1</sup> d <sub>1</sub>	<sup>2</sup> d <sub>2</sub> Thread	d <sub>3</sub>	l <sub>1</sub>	l <sub>2</sub> ±1	l <sub>3</sub> ±1	A/F	t min.
25 0.98	M 6	10 0.39	11 0.43	37.5 1.48	15 0.59	8	10 0.39
32 1.26	M 8	13 0.51	13 0.51	48 1.89	19 0.75	10	12 0.47
40 1.57	M 10	16 0.63	14 0.55	61 2.40	24 0.94	14	16 0.63
50 1.97	M 12	20 0.79	21 0.83	78 3.07	31 1.22	17	16 0.63

**Specification**

- Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 230 °F (110 °C)  
- Black, shiny finish
- **GN 319.2**  
Spindle  
Steel, zinc plated, blue passivated finish
- **GN 319.5**  
Spindle  
Stainless steel AISI 303  
Matte shot-blasted finish
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- RoHS compliant

**Information**

GN 319.2 and GN 319.5 both the threaded spindle and tapped spindle type revolving ball knobs can be utilized instead of revolving handles e.g., with handwheels or crank handles.

Revolving ball knobs have the same thread assembly dimensions as the DIN 39, DIN 98, and GN 598 fixed and revolving handles.

see also...

- *Softline Revolving Mushroom Shaped Knobs EN 597.1* → page [www.jwwinco.com](http://www.jwwinco.com)

<b>How to order (Inch, steel)</b>	<b>1</b> Ball diameter d <sub>1</sub>
<sup>1</sup> <sup>2</sup> <sup>3</sup>	<b>2</b> Thread d <sub>2</sub>
<b>GN 319.2-40-3/8X16-B</b>	<b>3</b> Type

<b>How to order (Metric, stainless steel)</b>	<b>1</b> Ball diameter d <sub>1</sub>
<sup>1</sup> <sup>2</sup> <sup>3</sup>	<b>2</b> Thread d <sub>2</sub>
<b>GN 319.5-32-M8-B</b>	<b>3</b> Type