



Metric



SS

Stainless Steel

3

Type

A

Without slot

N

With slot

Metric table

1	2	Dimensions in: millimeters - inches							
Length l ≈	d1 H9 Bore	d2	h1	h2 ≈	h3 ≈	h4 ≈	t +0.5	Ø Handle	Socket cap screw DIN 912
63 2.48	B 10	18 0.71	28 1.10	18 0.71	74 2.91	40 1.57	18 0.71	18 0.71	M 5
80 3.15	B 10	18 0.71	28 1.10	18 0.71	74 2.91	40 1.57	18 0.71	18 0.71	M 5
100 3.94	B 12	20 0.79	30 1.18	20 0.79	88 3.46	50 1.97	20 0.79	21 0.83	M 6
125 4.92	B 12	20 0.79	30 1.18	20 0.79	88 3.46	50 1.97	20 0.79	21 0.83	M 6

Specification

- Crank body  
Stainless steel AISI 304  
Shot-blasted
- Crank arm and hub  
Butt-welded
- Cover cap  
Plastic, black
- Cylindrical revolving handle  
Plastic  
Duroplast (Phenolic PF)  
- Black, shiny finish  
- Temperature resistant up to 230 °F (110 °C)
- Cross Holes GN 110 → page 2042
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 369.5 commercial crank handles feature a compact design and are used for light drive and adjustment tasks. Due to the materials used, these crank handles are also suitable for aggressive environments.

The slot of type N easily transfers the rotary movement to the shaft by means of a cross pin mounted on the shaft. The crank handle can be mounted removably or permanently assembled axially with a DIN 912 socket cap screw. Type A can be ordered with GN 110 cross holes.

Thanks to the simple manufacturing process it is relatively easy and inexpensive to produce customized designs of these crank handles.

see also...

- Crank Handles EN 670.2 (Technopolymer Plastic) → [www.jwwinco.com](http://www.jwwinco.com)
- Crank Handles GN 471 (Aluminum) → page 282

How to order	1	Length l
	2	Bore d1
	3	Type
GN 369.5-125-B12-A		