



SS Stainless Steel

4 Type

- C** With tapped hole
- K** With blind bore H7

Metric table

Dimensions in: millimeters - inches

² d_1	³ d_2 Type C	³ d_3 H7 Type K	$d_4 \approx$	$h \approx$	t_1 min.	t_2 min.
16 0.63	M 4	B 6	8 0.31	15 0.59	7 0.28	9 0.35
20 0.79	M 5	B 8	12 0.47	18 0.71	9 0.35	11 0.43
25 0.98	M 6	B 10	15 0.59	22.5 0.89	11 0.43	14 0.55
32 1.26	M 8	B 12	18 0.71	29 1.14	14.5 0.57	17 0.67
40 1.57	M 10	B 16	22 0.87	37 1.46	18 0.71	22 0.87
50 1.97	M 12*	B 20	27 1.06	46 1.81	21 0.83	28 1.10

* This size is only available in steel and aluminum.

Specification

- Steel **ST**
Turned and polished finish
- Aluminum **AL**
Turned and polished finish
- Stainless steel AISI 303 **NI**
Matte shot-blasted finish
- *ISO Fundamental Tolerances* → page 2129
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- For certain minimum quantities, steel ball knobs can also be supplied plated.

Information

Metal ball knobs, instead of plastic ball knobs, are suitable for heavy duty application uses. The stainless steel option is an excellent choice for corrosion-free applications.

How to order	
¹	Material
²	Ball diameter d_1
³	Thread d_2 (Bore diameter d_3)
⁴	Type

DIN 319-¹NI-²40-³M10-⁴C