

**4 Type (Base)**

- A0** Without rubber pad / cap
- B0** Without rubber pad / cap, with 2 mounting holes
- A1** With rubber cap, clipped on, black
- A3** With rubber pad, vulcanized, black

**Inch table**

d <sub>1</sub>	d <sub>2</sub> Thread	l <sub>1</sub>								l <sub>7</sub> Version X	d <sub>3</sub>	h <sub>1</sub>	h <sub>6</sub>	m	s
		Version S / SK				Version U / UK									
1.57 40	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.21 5.4	0.08 2	0.14 3.5	1.18 30	0.06 1.5
1.57 40	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.21 5.4	0.08 2	0.14 3.5	1.18 30	0.06 1.5
1.57 40	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.22 31	0.21 5.4	0.08 2	0.14 3.5	1.18 30	0.06 1.5
1.57* 40	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.21 5.4	0.08 2	0.14 3.5	1.18 30	0.06 1.5
1.97 50	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.26 6.6	0.10 2.5	0.16 4	1.50 38	0.08 2
1.97 50	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.26 6.6	0.10 2.5	0.16 4	1.50 38	0.08 2
1.97 50	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.26 6.6	0.10 2.5	0.16 4	1.50 38	0.08 2
1.97 50	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.26 6.6	0.10 2.5	0.16 4	1.50 38	0.08 2
2.36 60	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.26 6.6	0.10 2.5	0.18 4.5	1.89 48	0.08 2
2.36 60	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.26 6.6	0.10 2.5	0.18 4.5	1.89 48	0.08 2
2.36 60	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.26 6.6	0.10 2.5	0.18 4.5	1.89 48	0.08 2
2.36 60	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.26 6.6	0.10 2.5	0.18 4.5	1.89 48	0.08 2
3.15 80	5/16 x 18	-	-	-	-	-	-	-	-	1.02 26	0.34 8.6	0.12 3	0.20 5	2.52 64	0.08 2
3.15 80	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.14 29	0.34 8.6	0.12 3	0.20 5	2.52 64	0.08 2
3.15 80	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.34 8.6	0.12 3	0.20 5	2.52 64	0.08 2
3.15 80	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.50 38	0.34 8.6	0.12 3	0.20 5	2.52 64	0.08 2
3.15 80	3/4 x 10	-	-	-	-	3.94 100	4.92 125	5.91 150	-	1.77 45	0.34 8.6	0.12 3	0.20 5	2.52 64	0.08 2

\* Not available in type B0

d <sub>1</sub>	d <sub>2</sub> Thread	h <sub>3</sub>	h <sub>4</sub>	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>7</sub>	t
1.57 40	5/16 x 18	-	-	-	-	-	1/2	0.31 8
1.57 40	3/8 x 16	0.43 11	-	11/16	-	-	1/2	0.39 10
1.57 40	1/2 x 13	0.43 11	-	11/16	-	-	5/8	0.47 12
1.57 40	5/8 x 11	-	0.67 17	-	1/2	5/16	7/8	0.63 16
1.97 50	5/16 x 18	-	-	-	-	-	1/2	0.31 8
1.97 50	3/8 x 16	0.43 11	-	11/16	-	-	1/2	0.39 10
1.97 50	1/2 x 13	0.43 11	-	11/16	-	-	5/8	0.47 12
1.97 50	5/8 x 11	-	0.67 17	-	1/2	5/16	7/8	0.63 16
2.36 60	5/16 x 18	-	-	-	-	-	1/2	0.31 8
2.36 60	3/8 x 16	0.43 11	-	11/16	-	-	1/2	0.39 10
2.36 60	1/2 x 13	0.43 11	-	11/16	-	-	5/8	0.47 12
2.36 60	5/8 x 11	-	0.67 17	-	1/2	5/16	7/8	0.63 16
3.15 80	5/16 x 18	-	-	-	-	-	1/2	0.31 8
3.15 80	3/8 x 16	0.47 12	-	11/16	-	-	1/2	0.39 10
3.15 80	1/2 x 13	0.47 12	-	11/16	-	-	5/8	0.47 12
3.15 80	5/8 x 11	-	0.71 18	-	1/2	5/16	7/8	0.63 16
3.15 80	3/4 x 10	-	0.75 19	-	9/16	7/16	1	0.79 20

3.1

3.2

3.3

3.4

3.5

3.6

3.7

3.8

3.9

3.10



Stud / socket versions		
<p><b>S</b> Without nut <b>SK</b> With nut</p>	<p><b>U</b> Without nut <b>UK</b> With nut</p>	<p><b>X</b> Tapped socket type</p>
External hex at the bottom at $d_2$ 3/8 x 16, 1/2 x 13 M 8, M 10, M 12	Internal hex at the top, wrench flat at the bottom at $d_2$ 5/8 x 11, 3/4 x 10 M 16, M 20, M 24	External hex with tapped socket at $d_2$ 5/16 x 18, 3/8 x 16, 1/2 x 13, 5/8 x 11, 3/4 x 10 M 8, M 10, M 12, M 16, M 20

**Metric table**

d <sub>1</sub>	d <sub>2</sub> Thread	l <sub>1</sub> Version S / SK										Version U / UK										l <sub>7</sub> Version X	d <sub>3</sub>	h <sub>1</sub>	h <sub>6</sub>	m	s
		40	50	63	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-						
40 1.57	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	25 0.98	5.4 0.21	2 0.08	3.5 0.14	30 1.18	1.5 0.06								
40 1.57	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	28 1.10	5.4 0.21	2 0.08	3.5 0.14	30 1.18	1.5 0.06								
40 1.57	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	31 1.22	5.4 0.21	2 0.08	3.5 0.14	30 1.18	1.5 0.06								
40* 1.57	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	37 1.46	5.4 0.21	2 0.08	3.5 0.14	30 1.18	1.5 0.06										
50 1.97	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	25 0.98	6.6 0.26	2.5 0.10	4 0.16	38 1.50	2 0.08								
50 1.97	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	28 1.10	6.6 0.26	2.5 0.10	4 0.16	38 1.50	2 0.08								
50 1.97	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	32 1.26	6.6 0.26	2.5 0.10	4 0.16	38 1.50	2 0.08								
50 1.97	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	37 1.46	6.6 0.26	2.5 0.10	4 0.16	38 1.50	2 0.08										
60 2.36	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	25 0.98	6.6 0.26	2.5 0.10	4.5 0.18	48 1.89	2 0.08								
60 2.36	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	28 1.10	6.6 0.26	2.5 0.10	4.5 0.18	48 1.89	2 0.08								
60 2.36	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	32 1.26	6.6 0.26	2.5 0.10	4.5 0.18	48 1.89	2 0.08								
60 2.36	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	37 1.46	6.6 0.26	2.5 0.10	4.5 0.18	48 1.89	2 0.08										
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	26 1.02	8.6 0.34	3 0.12	5 0.20	64 2.52	2 0.08								
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	29 1.14	8.6 0.34	3 0.12	5 0.20	64 2.52	2 0.08								
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	32 1.26	8.6 0.34	3 0.12	5 0.20	64 2.52	2 0.08								
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	38 1.50	8.6 0.34	3 0.12	5 0.20	64 2.52	2 0.08										
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	45 1.77	8.6 0.34	3 0.12	5 0.20	64 2.52	2 0.08										
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	300 11.81	-	-	8.6 0.34	3 0.12	5 0.20	64 2.52	2 0.08										

\* Not available in type B0

d <sub>1</sub>	d <sub>2</sub> Thread	h <sub>3</sub>	h <sub>4</sub>	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>7</sub>	t
40 1.57	M 8	11 0.43	-	17 0.67	-	-	14 0.55	8 0.31
40 1.57	M 10	11 0.43	-	17 0.67	-	-	14 0.55	10 0.39
40 1.57	M 12	11 0.43	-	17 0.67	-	-	17 0.67	12 0.47
40 1.57	M 16	-	17 0.67	-	12 0.47	8 0.31	22 0.87	16 0.63
50 1.97	M 8	11 0.43	-	17 0.67	-	-	14 0.55	8 0.31
50 1.97	M 10	11 0.43	-	17 0.67	-	-	14 0.55	10 0.39
50 1.97	M 12	11 0.43	-	17 0.67	-	-	17 0.67	12 0.47
50 1.97	M 16	-	17 0.67	-	12 0.47	8 0.31	22 0.87	16 0.63
60 2.36	M 8	11 0.43	-	17 0.67	-	-	14 0.55	8 0.31
60 2.36	M 10	11 0.43	-	17 0.67	-	-	14 0.55	10 0.39
60 2.36	M 12	11 0.43	-	17 0.67	-	-	17 0.67	12 0.47
60 2.36	M 16	-	17 0.67	-	12 0.47	8 0.31	22 0.87	16 0.63
80 3.15	M 8	12 0.47	-	17 0.67	-	-	14 0.55	8 0.31
80 3.15	M 10	12 0.47	-	17 0.67	-	-	14 0.55	10 0.39
80 3.15	M 12	12 0.47	-	17 0.67	-	-	17 0.67	12 0.47
80 3.15	M 16	-	18 0.71	-	12 0.47	8 0.31	22 0.87	16 0.63
80 3.15	M 20	-	19 0.75	-	15 0.59	10 0.39	27 1.06	20 0.79
80 3.15	M 24	-	22 0.87	-	19 0.75	12 0.47	-	-

**Specification**

- Base  
Steel, zinc plated, blue passivated finish
- Threaded stud / tapped socket  
Steel, zinc plated, blue passivated finish
- Inch size hex nut ANSI / ASME B18.2.2  
Steel, zinc plated, blue passivated finish
- Metric size hex nut ISO 4032  
Steel, zinc plated, blue passivated finish
- Rubber cap  
TPE (Santoprene®) ≈ 80 shore A  
- Clipped on  
- Black
- Rubber pad  
NBR (Perbunan®) 70 ±5 shore A  
- Vulcanized, non-skid  
- Black
- Load Rating Information → page 2120
- Plastic Characteristics → page 2135
- RoHS compliant


**Information**


GN 40 leveling feet are simple, economically priced components and can be used universally thanks to the wide range of possible combinations of the base and the stud / socket versions. The base with rubber pad / cap protects sensitive surfaces and reduces lateral slippage. The type B0 can also be fastened to the mounting surface via the two mounting holes provided.

These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- Leveling Feet GN 42 (Steel, with Mounting Hole) → page 1526 / 1530
- Leveling Feet GN 41 (Stainless Steel AISI 304, without Mounting Hole) → page 1520
- Leveling Feet GN 44 / GN 45 (Stainless Steel AISI 316, with / without Mounting Hole) → page 1524 / 1540
- Threaded Tube Ends EN 448 (Plastic) → page 1578 / 1578
- Threaded Tube Inserts GN 992 / GN 922.5 (Aluminum / Stainless Steel) → page 1581

<p>How to order (Inch)</p>  <p><b>GN 40-40-3/8X16-75-A0-S</b></p>	1 Base diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>
	3 Length l <sub>1</sub> (Length l <sub>7</sub> )
	4 Type (Base)
	5 Stud / socket version

<p>How to order (Metric)</p>  <p><b>GN 40-80-M20-200-A3-U</b></p>	1 Base diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>
	3 Length l <sub>1</sub> (Length l <sub>7</sub> )
	4 Type (Base)
	5 Stud / socket version

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

