



SS Stainless Steel

3 Type

- A** Mounting from the back with thread
- B** Mounting the operator's side with through hole
- C** Mounting from the operator's side by welding

4 Identification no.

- 1** Handle 90° foldaway
- 2** Handle 90° foldaway, with retaining springs
- 3** Handle 180° foldaway
- 4** Handle 180° foldaway, with retaining springs

Metric table

Dimensions in: millimeters - inches

Length l	b ₁	b ₂	b ₃	d ₁	d ₂	h ₁	h ₂ ≈	h ₃	h ₄	m	t ₁	t ₂
120 4.72	124 4.88	20 0.79	106 4.17	M 6	6.4 0.25	16 0.63	53 2.09	49 1.93	59 2.32	60 2.36	10 0.39	9.6 0.38

Specification

- Attachment part
Stainless steel precision casting **NI**
AISI CF-8
- Matte, shot-blasted finish **GS**
- Powder coated
Black, RAL 9005, textured finish **●SW**
(only Type A and B)
- Folding handle
Stainless steel AISI 304
Matte shot-blasted finish
- Retaining springs
Spring steel
Stainless steel AISI 301
- Load Rating Information → page 2068
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

GN 425.9 folding handles are used where the handle must only protrude a short distance in the resting position.

Folding handles identification numbers 1 and 2 are suitable for side “access”, as these have a 90° limit stop. If used from above, identification numbers 3 and 4 with a handle that can fold freely through 180° are a better version.

The retaining springs of identification numbers 2 and 4 keep the handle in any position. This keeps the handle in a position that can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

see also...

- Folding Handles with Recessed Tray GN 425.8 (Steel / Stainless Steel) → page 163

How to order	1 Length l
	2 Material
	3 Type
	4 Identification no.
	5 Finish

1 2 3 4 5
GN 425.9-120-NI-A-1-SW