




Identification no. 1 / 2





Type A




Metric



Identification no. 3 / 4



Type B




SS Stainless Steel

3 Type

- A** Mounting from the back with thread
- B** Mounting the operator's side with through hole
- C** Mounting from the operator's side by welding

4 Identification no.

- 1** Handle 90° foldaway
- 2** Handle 90° foldaway, with retaining springs
- 3** Handle 180° foldaway
- 4** Handle 180° foldaway, with retaining springs



Type C



Metric table



Dimensions in: millimeters / inches

Length l	b ₁	b ₂	b ₃	d ₁	d ₂	h ₁	h ₂ ≈	h ₃	h ₄	m	t ₁	t ₂
120 4.72	124 4.88	20 0.79	106 4.17	M 6	6.4 0.25	16 0.63	53 2.09	49 1.93	59 2.32	60 2.36	10 0.39	9.6 0.38

Specification



Attachment part

Stainless steel
precision casting AISI CF-8
• Matte shot-blasted finish
• Powder coated
Black, RAL 9005, textured finish
(only in type A and B)

NI

GS

● SW

Folding handle

Stainless steel AISI 304
Matte shot-blasted finish

Retaining springs

Spring steel AISI 301

RoHS

Folding handles GN 425.9 are used where the handle must only protrude a short distance in the resting position.

Folding handles identification numbers 1 and 2 are suitable for side "access", as these have a 90° limit stop. If used from above, identification numbers 3 and 4 with a handle that can fold freely through 180° are a better version.

The retaining springs of identification numbers 2 and 4 keep the handle in any position. This keeps the handle in a position that can be easily accessed and prevents noise as a result of vibration in the resting position.

The handle and the retaining springs are secured by mounting the attachment across the entire surface. All components are supplied unassembled.

see also...

Page

GN 425.8 Folding Handles with Recessed Tray
(Steel / Stainless Steel, with Handle Held or Spring Return)

QVX

Technical Information

Load Capacity Information
Stainless Steel Characteristics

QVX

QVX

How to order

GN 425.9-120-NI-A-1-SW

1	Length l
2	Material
3	Type
4	Identification no.
5	Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

