



- 2 Type**
- A** Mounting from the back (tapped blind hole)
 - B** Mounting from the operator's side

Metric table

Dimensions in: millimeters - inches

l₁	a	b	d₁ Type A	d₂ Type B	h₁	h₂	l₂	t
120 4.72	14 0.55	22 0.87	M 6	6.5 0.26	44 1.73	5 0.20	141.2 5.56	13 0.51
140 5.51	18 0.71	28 1.10	M 8	8.5 0.33	55 2.17	6 0.24	166.5 6.56	17 0.67

Specification

- **GN 328**
Aluminum die-cast
- Powder coated
 Black, RAL 9005, textured finish ● **SW**
 Silver, RAL 9006, textured finish ● **SR**
- Plain, tumbled finish ● **BL**
- **GN 328.5**
Stainless steel precision casting AISI 316
Matte shot-blasted finish ● **GS**
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

On request

- Other finishes

Information

GN 328 and GN 328.5 cabinet "U" handles have excellent stability and ergonomic design. The finger recesses on the underside of the handle provide an especially comfortable grip.

In combination with the larger GN 428 cabinet "U" handle, they meet the requirements of modern industrial design.

see also...

- *Cabinet "U" Handles GN 565* → page 98
- *Cabinet "U" Handles GN 428* → page 153

How to order (Aluminum) GN 328-120-A-SW	1 Length l ₁
	2 Type
	3 Finish

How to order (Stainless steel) GN 328.5-140-B-GS	1 Length l ₁
	2 Type
	3 Finish