



Metric table

<div>2</div>		<div>3</div>		Dimensions in: millimeters / inches													
d ₁	Length l					a min.	b	d ₂	d ₃	d ₄	d ₅	d ₆	h ₁	h ₂	m	A/F	t min.
30 1.18	300 11.81	400 15.75	500 19.69	600 23.62	70 2.76	27.5 1.08	M 10	46 1.81	46.6 1.83	42 1.65	8 0.31	60 2.36	84 3.31	13.5 0.53	5	20 0.79	
40 1.57	400 15.75	600 23.62	800 31.50	1000 39.37	70 2.76	30 1.18	M 12	56 2.20	56.8 2.24	50 1.97	8 0.31	70 2.76	99 3.90	18.5 0.73	5	25 0.98	

Specification		1	4	5
Handle tube				
Stainless steel AISI 304				
Ground, matte finish (Ra < 0.8 µm)				
Handle legs				
Stainless steel AISI 304				
Matte finish (Ra < 0.8 µm)				
Sealing ring / Wiper				
TPU				
• Blue				
• Operating temperature				
-4 °F to +230 °F (-20 °C to +110 °C)				
• Hardness 95 ±5 Shore A				
• FDA compliant				
Clamping wedge				
Brass				
Set screw				
Stainless steel				
RoHS				

Tubular handles GN 3330 comply with the DGV testing principles and are designed for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the non-concave geometry prevent adherence of dirt and facilitate cleaning. The movable handle legs are loosely enclosed for fastening to the handle tube using the integrated clamping wedge during installation. The position of the handle legs can be adjusted as required, but must not be less than the minimum distance a, as the tubes may be undersized in the edge area. For large lengths or loads, additional movable handle legs can be added. These are available under standard part number GN 3331.	
Technical Information	
Product Family Hygienic Design	QVX
Plastic Characteristics	QVX
Stainless Steel Characteristics	QVX
Accessory	
GN 1580 Hex Head Screws	QVX
GN 1581 Hex Head Screws	QVX
GN 3331 Straight Handle Legs	QVX

How to order	
1	Material
2	Handle diameter d ₁
3	Length l
4	Finish
5	Sealing ring material

GN 3330-NI-40-1000-MT-T