



SS Stainless Steel

**4 Type (Base)**

- D0** Without rubber pad / cap
- D1** With rubber cap, clipped on, black
- D3** With rubber pad, vulcanized, black

**Inch table**

d <sub>1</sub>	d <sub>2</sub> Thread	l <sub>1</sub>								l <sub>7</sub> Version X	d <sub>3</sub>	h <sub>1</sub>	h <sub>6</sub>	l <sub>8</sub>	m	r	s
		Version S / SK				Version U / UK											
1.97 50	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
1.97 50	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.51 13	0.10 2.5	0.16 4	2.36 60	1.77 45	0.59 15	0.08 2
2.36 60	5/16 x 18	-	-	-	-	-	-	-	-	0.98 25	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.10 28	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
2.36 60	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.46 37	0.51 13	0.10 2.5	0.18 4.5	2.56 65	1.97 50	0.59 15	0.08 2
3.15 80	5/16 x 18	-	-	-	-	-	-	-	-	1.02 26	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.14 29	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.50 38	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2
3.15 80	3/4 x 10	-	-	-	-	3.94 100	4.92 125	5.91 150	-	1.77 45	0.51 13	0.12 3	0.20 5	3.35 85	2.76 70	0.59 15	0.08 2

Dimensions in: inches - millimeters

d <sub>1</sub>	d <sub>2</sub> Thread	h <sub>3</sub>	h <sub>4</sub>	h <sub>5</sub>	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>7</sub>	t
1.97 50	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
1.97 50	3/8 x 16	0.43 11	-	-	11/16	-	-	1/2	0.39 10
1.97 50	1/2 x 13	0.43 11	-	-	11/16	-	-	5/8	0.47 12
1.97 50	5/8 x 11	-	0.67 17	0.55 14	-	1/2	5/16	7/8	0.63 16
2.36 60	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
2.36 60	3/8 x 16	0.43 11	-	-	11/16	-	-	1/2	0.39 10
2.36 60	1/2 x 13	0.43 11	-	-	11/16	-	-	5/8	0.47 12
2.36 60	5/8 x 11	-	0.67 17	0.55 14	-	1/2	5/16	7/8	0.63 16
3.15 80	5/16 x 18	-	-	-	-	-	-	1/2	0.31 8
3.15 80	3/8 x 16	0.47 12	-	-	11/16	-	-	1/2	0.39 10
3.15 80	1/2 x 13	0.47 12	-	-	11/16	-	-	5/8	0.47 12
3.15 80	5/8 x 11	-	0.71 18	0.59 15	-	1/2	5/16	7/8	0.63 16
3.15 80	3/4 x 10	-	0.75 19	0.59 15	-	9/16	7/16	1	0.79 20

Stud / socket versions		
<p><b>S</b> Without nut <b>SK</b> With nut</p>	<p><b>T*</b> Without nut <b>TK*</b> With nut</p>	<p><b>U</b> Without nut <b>UK</b> With nut</p>
External hex at the bottom at d <sub>2</sub> 3/8 x 16, 1/2 x 13 M 8, M 10, M 12	Wrench flat at the bottom at d <sub>2</sub> - M 16, M 20, M 24	Internal hex at the top, wrench flat at the bottom at d <sub>2</sub> 5/8 x 11, 3/4 x 10 M 16, M 20, M 24
<p><b>V*</b> Without nut <b>VK*</b> With nut</p>	<p><b>W*</b> With adjustable sleeve</p>	<p><b>X</b> Tapped socket type</p>
External hex at the top, wrench flat at the bottom at d <sub>2</sub> - M 16, M 20, M 24	Covered thread, wrench flat at the bottom at d <sub>2</sub> - M 16, M 20, M 24	External hex with tapped socket at d <sub>2</sub> 5/16 x 18, 3/8 x 16, 1/2 x 13, 5/8 x 11, 3/4 x 10 M 8, M 10, M 12, M 16, M 20

\* Only available with Metric thread

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10



**Metric table**

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub>	l <sub>1</sub>	Version T / TK and U / UK								Version V / VK				Version W				l <sub>7</sub>	
			Version S / SK				Version T / TK and U / UK				Version V / VK				Version W					
50 1.97	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	25 0.98
50 1.97	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	28 1.10
50 1.97	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26
50 1.97	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-	-	-	-	-	-	-	-	37 1.46
60 2.36	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	25 0.98
60 2.36	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	28 1.10
60 2.36	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26
60 2.36	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	37 1.46
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	26 1.02
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	-	29 1.14
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	38 1.50
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	100 3.94	125 4.92	150 5.91	200 7.87	134 5.28	159 6.26	184 7.24	234 9.21	45 1.77
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	300 11.81	-	100 3.94	150 5.91	200 7.87	-	159 6.26	209 8.23	259 10.20	-	-

d <sub>1</sub>	d <sub>2</sub> Thread	d <sub>3</sub>	d <sub>5</sub>	h <sub>1</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>5</sub>	h <sub>6</sub>	l <sub>4</sub>	l <sub>5</sub>	l <sub>6</sub>	l <sub>8</sub>	A/F <sub>1</sub>	A/F <sub>2</sub>	A/F <sub>3</sub>	A/F <sub>4</sub>	A/F <sub>5</sub>	A/F <sub>6</sub>	A/F <sub>7</sub>	m	r	s	t	
50 1.97	M 8	13 0.51	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	60 2.36	17 0.67	-	-	-	-	-	-	14 0.55	45 1.77	15 0.59	2 0.08	8 0.31
50 1.97	M 10	13 0.51	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	60 2.36	17 0.67	-	-	-	-	-	-	14 0.55	45 1.77	15 0.59	2 0.08	10 0.39
50 1.97	M 12	13 0.51	-	2.5 0.10	11 0.43	-	-	4 0.16	-	-	-	60 2.36	17 0.67	-	-	-	-	-	-	17 0.67	45 1.77	15 0.59	2 0.08	12 0.47
50 1.97	M 16	13 0.51	-	2.5 0.10	-	17 0.67	14 0.55	4 0.16	-	-	-	60 2.36	-	12 0.47	8 0.31	-	-	-	-	22 0.87	45 1.77	15 0.59	2 0.08	16 0.63
60 2.36	M 8	13 0.51	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	65 2.56	17 0.67	-	-	-	-	-	-	14 0.55	50 1.97	15 0.59	2 0.08	8 0.31
60 2.36	M 10	13 0.51	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	65 2.56	17 0.67	-	-	-	-	-	-	14 0.55	50 1.97	15 0.59	2 0.08	10 0.39
60 2.36	M 12	13 0.51	-	2.5 0.10	11 0.43	-	-	4.5 0.18	-	-	-	65 2.56	17 0.67	-	-	-	-	-	-	17 0.67	50 1.97	15 0.59	2 0.08	12 0.47
60 2.36	M 16	13 0.51	0.94	2.5 0.10	-	17 0.67	14 0.55	4.5 0.18	45 1.77	45 1.77	29 1.14	65 2.56	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	50 1.97	15 0.59	2 0.08	16 0.63	
80 3.15	M 8	13 0.51	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	85 3.35	17 0.67	-	-	-	-	-	-	14 0.55	70 2.76	15 0.59	2 0.08	8 0.31
80 3.15	M 10	13 0.51	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	85 3.35	17 0.67	-	-	-	-	-	-	14 0.55	70 2.76	15 0.59	2 0.08	10 0.39
80 3.15	M 12	13 0.51	-	3 0.12	12 0.47	-	-	5 0.20	-	-	-	85 3.35	17 0.67	-	-	-	-	-	-	17 0.67	70 2.76	15 0.59	2 0.08	12 0.47
80 3.15	M 16	13 0.51	0.94	3 0.12	-	18 0.71	15 0.59	5 0.20	45 1.77	45 1.77	29 1.14	85 3.35	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	70 2.76	15 0.59	2 0.08	16 0.63	
80 3.15	M 20	13 0.51	1.18	3 0.12	-	18 0.71	15 0.59	5 0.20	56 2.20	56 2.20	37 1.46	85 3.35	-	15 0.59	10 0.39	13 0.51	16 0.63	24 0.94	27 1.06	70 2.76	15 0.59	2 0.08	20 0.79	
80 3.15	M 24	13 0.51	1.38	3 0.12	-	21 0.83	18 0.71	5 0.20	67 2.64	67 2.64	42 1.65	85 3.35	-	19 0.75	12 0.47	17 0.67	20 0.79	30 1.18	-	70 2.76	15 0.59	2 0.08	-	

**Specification**

- Base  
Stainless steel AISI 304  
Plain, tumbled finish
- Threaded stud / tapped socket  
Stainless steel AISI 304
- Inch size hex nut ANSI / ASME B18.2.2  
Stainless steel AISI 304
- Metric size hex nut ISO 4032  
Stainless steel AISI 304
- Rubber cap  
TPE (Santoprene®) ≈ 80 shore A  
- Clipped on  
- Black
- Rubber pad  
NBR (Perbunan®) 70 ±5 shore A  
- Vulcanized, non-skid  
- Black
- Load Rating Information → page 2121
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**On request**

- Stud versions T / TK, V / VK and W with Inch thread with certain minimum quantities

**Information**

GN 43 leveling feet are intended for use in aggressive environments. The wide range of possible combinations of the base and the stud / socket versions make these leveling feet universally applicable.

The leveling feet can be screwed to the mounting surface using the mounting hole, which prevents lateral slippage. The base with rubber pad / cap also protects sensitive surfaces.

These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- Leveling Feet GN 42 (Steel, with Mounting Hole) → page 1526
- Leveling Feet GN 42 (Steel, with Slotted Mounting Hole, Rectangular Shape) → page 1526
- Leveling Feet GN 41 (Stainless Steel AISI 304, without Mounting Hole) → page 1520
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Slotted Mounting Hole, Rectangular Shape) → page 1536
- Leveling Feet GN 44 / GN 45 (Stainless Steel AISI 316, with / without Mounting Hole) → page 1524 / 1540
- Threaded Tube Ends EN 448 (Plastic) → page 1578 / 1578
- Threaded Tube Inserts GN 992.5 (Stainless Steel) → page 1581

<p>How to order (Inch)</p> <p><b>GN 43-50-5/16X18-25-D0-X</b></p>	1 Base diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>
	3 Length l <sub>7</sub> (Length l <sub>1</sub> )
	4 Type (Base)
	5 Stud / socket version

<p>How to order (Metric)</p> <p><b>GN 43-80-M16-100-D3-V</b></p>	1 Base diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>
	3 Length l <sub>2</sub> (Length l <sub>1</sub> , l <sub>3</sub> , l <sub>7</sub> )
	4 Type (Base)
	5 Stud / socket version

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10