



Metric table

2 3

Dimensions in: millimeters - inches

d ₁	Length l					a min.	b	d ₂	d ₃	d ₄	d ₅	d ₆	h ₁	h ₂	m	A/F	t min.
30	300	400	500	600		70	27.5	M 10	46	46.6	42	8	60	84	13.5	5	20
1.18	11.81	15.75	19.69	23.62		2.76	1.08		1.81	1.83	1.65	0.31	2.36	3.31	0.53		0.79
40	400	600	800	1000		70	30	M 12	56	56.8	50	8	70	99	18.5	5	25
1.57	15.75	23.62	31.50	39.37		2.76	1.18		2.20	2.24	1.97	0.31	2.76	3.90	0.73		0.98

Specification

1 4 5

- Tube
Stainless steel AISI 304 **NI**
Ground, matte finish (Ra < 0.8 µm) **MT**
- Handle legs
Stainless steel AISI 304
Matte finish (Ra < 0.8 µm)
- Sealing ring and wiper
TPU **T**
- Blue
- Temperature resistant
-4 °F to +230 °F (-20 °C to +110 °C)
- Hardness 95 ±5 Shore A
- FDA compliant
- Clamping wedge
Brass
- Set screw
Stainless steel
- *Plastic Characteristics* → page QVX
- *Stainless Steel Characteristics* → page QVX
- **RoHS**

Information

Tubular handles GN 3330 are designed for use in hygienic areas. The sealed mounting surface enables fastening without dead spaces. The high quality finish as well as the non-concave geometry prevent adherence of dirt and facilitate cleaning.

The movable straight handle legs are loosely enclosed for fastening to the handle tube using the integrated clamping wedge during installation. The position of the handle legs can be adjusted as required, but must not be less than the minimum distance a, as the tubes may be undersized in the edge area.

For large lengths or loads, additional movable handle legs can be added. These are available under series number GN 3331.

see also...

- *Product Family Hygienic Design* → page QVX

Accessory

- Hex head screws GN 1580 → page QVX
- Hex head screws GN 1581 → page QVX
- Straight handle legs GN 3331 → page QVX

How to order	
1	Material
2	Handle diameter d ₁
3	Length l
4	Finish
5	Material (seals)

1 2 3 4 5
GN 3330-NI-40-1000-MT-T