



SS Stainless Steel

4 Type (Base)

- D0 Without rubber pad / cap
- B0 Without rubber pad / cap, with 2 mounting holes
- D1 With rubber cap, clipped on, black
- D3 With rubber pad, vulcanized, black

Metric table

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub> Thread	l <sub>1</sub> Version S / SK				Version T / TK						
40 1.57	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-
40 1.57	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-
40 1.57	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-
40* 1.57	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
50 1.97	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-
50 1.97	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-
50 1.97	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-
50 1.97	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
60 2.36	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-
60 2.36	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-
60 2.36	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-
60 2.36	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	300 11.81	-	-

\* Not available in type B0

d <sub>1</sub>	d <sub>2</sub> Thread			d <sub>3</sub>	h <sub>1</sub>	h <sub>3</sub>	h <sub>4</sub>	h <sub>6</sub>	m	s	A/F <sub>1</sub>	A/F <sub>2</sub>
40 1.57	M 8	M 10	M 12	5.4 0.21	2 0.08	11 0.43	-	3.5 0.14	30 1.18	1.5 0.06	17 0.67	-
40 1.57	M 16	-	-	5.4 0.21	2 0.08	-	17 0.67	3.5 0.14	30 1.18	1.5 0.06	-	12 0.47
50 1.97	M 8	M 10	M 12	6.6 0.26	2.5 0.10	11 0.43	-	4 0.16	38 1.50	2 0.08	17 0.67	-
50 1.97	M 16			6.6 0.26	2.5 0.10	-	17 0.67	4 0.16	38 1.50	2 0.08	-	12 0.47
60 2.36	M 8	M 10	M 12	6.6 0.26	2.5 0.10	11 0.43	-	4.5 0.18	48 1.89	2 0.08	17 0.67	-
60 2.36	M 16			6.6 0.26	2.5 0.10	-	17 0.67	4.5 0.18	48 1.89	2 0.08	-	12 0.47
80 3.15	M 8	M 10	M 12	8.5 0.33	3 0.12	12 0.47	-	5 0.20	64 2.52	2 0.08	17 0.67	-
80 3.15	M 16			8.5 0.33	3 0.12	-	18 0.71	5 0.20	64 2.52	2 0.08	-	12 0.47
80 3.15	M 20			8.5 0.33	3 0.12	-	19 0.75	5 0.20	64 2.52	2 0.08	-	15 0.59
80 3.15	M 24			8.5 0.33	3 0.12	-	22 0.87	5 0.20	64 2.52	2 0.08	-	19 0.75

**Stud versions**

**S** Without nut  
**SK** With nut

External hex at the bottom at d<sub>2</sub>  
M 8, M 10, M 12

**T** Without nut  
**TK** With nut

Wrench flat at the bottom at d<sub>2</sub>  
M 16, M 20, M 24

**Specification**

- Base  
Stainless steel AISI 316L  
Plain, tumbled finish
- Threaded stud  
Stainless steel AISI 316L
- Hex nut ISO 4032  
Stainless steel AISI 316L
- Rubber cap  
TPE (Santoprene®) ≈ 80 shore A  
- Clipped on  
- Black
- Rubber pad  
NBR (Perbunan®) 70 ±5 shore A  
- Vulcanized, non-skid  
- Black
- Load Rating Information → page 2121
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Information**

GN 44 leveling feet are intended for use in aggressive environments. The wide range of possible combinations of the base and the stud / socket versions make these leveling feet universally applicable. The base with the rubber pad / cap protects sensitive surfaces and reduces lateral slippage. The type B0 can also be fastened to the mounting surface via the two mounting holes provided. These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- Leveling Feet GN 40 (Steel, without Mounting Hole) → page 1516
- Leveling Feet GN 41 (Stainless Steel AISI 304, without Mounting Hole) → page 1520
- Leveling Feet GN 42 (Steel, with Mounting Hole) → page 1526
- Leveling Feet GN 42 (Steel, with Slotted Mounting Hole, Rectangular Shape) → page 1530
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Mounting Hole) → page 1532
- Leveling Feet GN 43 (Stainless Steel AISI 304, with Slotted Mounting Hole, Rectangular Shape) → page 1536
- Leveling Feet GN 45 (Stainless Steel AISI 316, with Mounting Hole) → page 1540

<p>How to order</p> <p>1 2 3 4 5</p> <p><b>GN 44-80-M20-150-D1-T</b></p>	1 Base diameter d <sub>1</sub>
	2 Thread d <sub>2</sub>
	3 Length l <sub>1</sub>
	4 Type (Base)
	5 Stud version

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10

