



3 Type

B Mounting on both sides

Metric table

Dimensions in: millimeters - inches

1 b_1	2 d_1	b_2	d_2 For screw	h_1	h_2	Length l	m_1	m_2	m_3
8 0.31	M 4	7 0.28	M 3	2.5 0.10	9.5 0.37	25 0.98	6 0.24	16 0.63	1.5 0.06
10 0.39	M 5	8 0.31	M 4	3.5 0.14	12 0.47	32 1.26	8 0.31	20 0.79	2 0.08
12 0.47	M 6	10 0.39	M 5	4 0.16	15 0.59	38 1.50	10 0.39	24 0.94	2.5 0.10
16 0.63	M 8	13 0.51	M 6	5 0.20	18.5 0.73	47 1.85	12 0.47	30 1.18	3 0.12
20 0.79	M 10	16 0.63	M 8	6 0.24	23 0.91	60 2.36	15 0.59	38 1.50	4 0.16

Specification

- Stainless steel precision casting AISI CF-8 **NI**
Matte shot-blasted finish **GS**
- Stainless Steel Characteristics → page QVX
- RoHS

Information

Mounting blocks GN 3492 quickly and easily fasten standard parts with external thread, such as ball plungers or setting bolts, perpendicular to the mounting plane. The slotted holes and the locating thread allow for positioning of the mounting blocks in two directions.

To prevent unintentional adjustment, the standard part can be secured with a clamping thread lock, a lock nut or a set screw.

see also...

- Product Family Standard Parts for Profile Systems → page QVX
- Ball Plungers GN 615 (with Slot) → page QVX
- Ball Plungers GN 615.3 (with Ball, with Internal Hex) → page QVX
- Threaded Flanges GN 3490 → page QVX

How to order	1	Width b_1
	2	Thread d_1
	3	Type
	4	Material
	5	Finish

GN 3492-12-M6-B-NI-GS