



Metric table

Dimensions in: millimeters - inches

¹ d ₁ Thread	² d ₂ H7	d ₃ -0.3	d ₄	Length l	s -0.15	t min.
M 6	8 0.31	18 0.71	8.5 0.33	19 0.75	9 0.35	9 0.35
M 8	10 0.39	20 0.79	11 0.43	24 0.94	12 0.47	11 0.43
M 10	12 0.47	25 0.98	13.5 0.53	28 1.10	14 0.55	14 0.55
M 12	16 0.63	32 1.26	16 0.63	34 1.34	17 0.67	16 0.63

Specification

- Steel
 - Property class 5
 - Blackened finish
- *ISO Fundamental Tolerances* → page QVX
- *Strength Values of Nuts* → page QVX
- **RoHS compliant**

On request

- For certain minimum quantities, inch size threads and bores

Information

In combination with set screws or double ended threaded studs (i.e. DIN 913 or DIN 6379), GN 444.2 eye nuts can be used as swing bolts in varying lengths.

In addition, used with a DIN 912 socket cap screw, a swiveling clamping screw can be produced.

Dimensions d₂, d₃ and s are identical to DIN 444.

For eye nut thread sizes M6, M8 M10 and M12, GN 732.1 cylinder head shoulder bolts can be used as bearing pins.

see also...

- *Set Screws GN 913.3* → page QVX
- *Double Ended Threaded Studs DIN 6379* → page QVX
- *Cylinder Head Shoulder Bolts GN 732.1* → page QVX
- *Joint Pieces GN 752* → page QVX

How to order ¹ ² GN 444.2-M10-12	1 Thread d ₁
	2 Eye diameter d ₂

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10