



**SS** Stainless Steel

**3 Type**

- D With plain stud
- E With threaded stud

**Metric table**

2

Dimensions in: millimeters - inches

d <sub>1</sub>	d <sub>2</sub> h8 Type D ST	d <sub>3</sub> Type E			d <sub>4</sub> h13	l <sub>1</sub> ≈	l <sub>2</sub>	l <sub>3</sub>	A/F Internal hex
		ST	A4	KT					
16 0.63	7 0.28	M 6	M 6	-	10 0.39	50 1.97	11 0.43	7 0.28	3
20 0.79	8 0.31	M 8	M 8	M 8	13 0.51	64 2.52	13 0.51	8 0.31	4
25 0.98	10 0.39	M 10	M 10	M 10	16 0.63	80 3.15	14 0.55	10 0.39	5
32 1.26	13 0.51	M 12	-	M 12	20 0.79	100 3.94	21 0.83	13 0.51	6
36 1.42	16 0.63	M 16	-	-	22 0.87	112 4.41	26 1.02	14 0.55	8

**Specification**

1

- Steel, zinc plated, blue passivated finish **ST**
- Stainless steel AISI 316L **A4**
- Plastic **KT**  
Technopolymer (Polyamide PA)  
- Temperature resistant up to 213 °F (100 °C)  
- Black, matte finish  
- Threaded stud  
Steel, blackened finish
- ISO Fundamental Tolerances → page 2129
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Information**

DIN 39 fixed handles are used in applications where a positive non-revolving grip is required. For hygienic reasons, a hexagonal recess is not used in type A4.

How to order <b>DIN39-ST-25-E</b>	1	Material
	2	Handle diameter d <sub>1</sub>
	3	Type

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4