



Adjustable lever kits GN 511



Application example



Retaining magnet GN 51.6



Metric table

Dimensions in: millimeters - inches

d ₁ Bore for shaft tolerance h11	b ₁	b ₂	d ₂	d ₃ Clamping thread	d ₄ For screw	l ₁	l ₂	l ₃	l ₄	m	s Square	Adjustable lever kit for d ₃
B 8	14 0.55	29 1.14	31.5 1.24	M 4	M 4	20 0.79	7 0.28	7 0.28	3 0.12	22 0.87	-	GN 511-M4-14
B 10	16 0.63	35 1.38	38 1.50	M 5	M 5	24 0.94	8 0.31	8 0.31	2.5 0.10	27 1.06	8 0.31	GN 511-M5-16
B 12	16 0.63	35 1.38	38 1.50	M 5	M 5	25 0.98	8 0.31	8 0.31	2.5 0.10	27 1.06	10 0.39	GN 511-M5-16
B 15	20 0.79	41 1.61	45 1.77	M 6	M 6	30 1.18	10 0.39	10 0.39	4 0.16	32 1.26	12 0.47	GN 511-M6-20
B 16	20 0.79	41 1.61	45 1.77	M 6	M 6	31 1.22	10 0.39	10 0.39	4 0.16	32 1.26	-	GN 511-M6-20
B 20	25 0.98	44 1.73	50 1.97	M 6	M 6	35 1.38	12.5 0.49	12.5 0.49	6.5 0.26	36 1.42	16 0.63	GN 511-M6-25

Specification

- Body
Aluminum
- Matte, tumbled finish
- Black anodized finish
- Socket cap screws DIN 912
Stainless steel AISI 304
- ISO Fundamental Tolerances → page 2129
- Stainless Steel Characteristics → page 2143
- RoHS compliant

MT
ELS

Accessory

- Adjustable lever kits GN 511 → page 1829

Information

GN 473 base plate mounting clamps have a horizontal and a vertical clamping bore. The vertical clamping bore can also fit square tubes.

The bore distance m corresponds to GN 477 mounting clamps, GN 485 base plate swivel mounting clamps, and GN 480 flanged mounting bolts as well as GN 51.6 retaining magnets.

In the standard version, the clamping screws are DIN 912 socket cap screws with hexagonal socket. They can be replaced by GN 511 adjustable lever kits (part number, see dimensional table).

see also...

- Product Family Standard Parts for Profile Systems → page 18
- Rods / Tubes GN 480.1 → page 1838
- Flanged Connector Clamps GN 145 → page 1778

How to order	1 Bore d ₁
	2 Finish

GN 473-B12-MT

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10