



**Metric table**

Dimensions in: millimeters - inches

1	2	3																
l <sub>1</sub>	d <sub>1</sub>	l <sub>2</sub>									d <sub>2</sub>	d <sub>3</sub>	d <sub>4</sub>	h <sub>1</sub>	h <sub>2</sub>	h <sub>3</sub>	h <sub>4</sub>	
																	Stroke	
42	M 5	10	16	20	-	-	-	-	-	-	12	18	16	27	6	32	3.5	
1.65		0.39	0.63	0.79							0.47	0.71	0.63	1.06	0.24	1.26	0.14	
42	M 6	10	16	20	25	30	40	-	-	-	12	18	16	27	6	32	3.5	
1.65		0.39	0.63	0.79	0.98	1.18	1.57				0.47	0.71	0.63	1.06	0.24	1.26	0.14	
63	M 6	10	16	20	25	30	40	-	-	-	15	23	20	34	8	43	4	
2.48		0.39	0.63	0.79	0.98	1.18	1.57				0.59	0.91	0.79	1.34	0.31	1.69	0.16	
63	M 8	16	20	25	30	35	40	45	50	60	15	23	20	34	8	43	4	
2.48		0.63	0.79	0.98	1.18	1.38	1.57	1.77	1.97	2.36	0.59	0.91	0.79	1.34	0.31	1.69	0.16	
80	M 10	20	25	30	35	40	50	60	70	-	19	28	24	42	10	54	4	
3.15		0.79	0.98	1.18	1.38	1.57	1.97	2.36	2.76		0.75	1.10	0.94	1.65	0.39	2.13	0.16	
80	M 12	20	25	30	35	40	50	60	70	80	19	28	24	42	10	54	4	
3.15		0.79	0.98	1.18	1.38	1.57	1.97	2.36	2.76	3.15	0.75	1.10	0.94	1.65	0.39	2.13	0.16	
100	M 12	30	50	70	-	-	-	-	-	-	25	33	31	48	12	65	5	
3.94		1.18	1.97	2.76							0.98	1.30	1.22	1.89	0.47	2.56	0.20	
100	M 16	30	50	70	-	-	-	-	-	-	25	33	31	48	12	65	5	
3.94		1.18	1.97	2.76							0.98	1.30	1.22	1.89	0.47	2.56	0.20	

**Specification**

- Lever body / serrated insert  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 266 °F (130 °C)  
- Black, RAL 9005, matte finish
- Threaded stud / retaining screw  
Steel, blackened finish
- Plastic Characteristics → page 2135
- RoHS compliant



**Information**

EN 500 adjustable levers have proven to be ideal wherever parts have to be clamped in a confined space or in a particular lever position. The insert is connected to the lever via serrations that can easily be disengaged.

Pulling the lever upwards disengages the serrations, allowing it to be swiveled to the ideal clamping position. When releasing the lever, the mating serrations of the lever and the insert automatically re-engage via a spring and screw that holds the assembly together.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Adjustable Levers EN 503 (with Push Button) → page 514

**On request**

- Levers in RAL 2004 orange and RAL 7031 gray

How to order	1	Lever length l <sub>1</sub>
	2	Thread d <sub>1</sub>
	3	Thread length l <sub>2</sub>
	4	Color

**EN 500-80-M10-40-SW**