



SS Stainless Steel

**Metric table**



Dimensions in: millimeters - inches

Length $l \pm 0.25$	$h_1$	$h_2$	$h_3$	$F_1$ Static load Folded out
100 3.94	34 1.34	44.5 1.75	55 2.17	500 N 112 lbf
120 4.72	34 1.34	44.5 1.75	55 2.17	500 N 112 lbf
180 7.09	34 1.34	44.5 1.75	55 2.17	500 N 112 lbf

**Specification**



- Handle
  - Steel
  - Chrome plated finish
  - Stainless steel AISI 303
  - Matte shot-blasted finish
- Attachment parts
  - Plastic, Polyamide (PA)
  - Operating temperature up to 212 °F (100 °C)
  - Black, matte finish
- Covers
  - Plastic, Polyamide (PA)
  - Operating temperature up to 212 °F (100 °C)
  - Black-gray, matte finish
- Load Rating Information → page 2068
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

CR  
NI

**Information**

GN 425.5 folding handles are used in applications where the handle must not protrude or protrude only slightly. The handle is held in both end positions by means of a spring-loaded (spring disks) thrust bolt. The static load capacity value given in the table is an approximate value which, if exceeded, may result in permanent deformation or fracture of the plastic attachment part. Folding handles GN 425.2 may be used as an alternative.

see also...

- Folding Cabinet "U" Handles GN 425.8 (Steel / Stainless Steel, with Locking or Spring-Loaded Return) → page 163
- Folding Handles EN 825.1 (Plastic, with Spring-Loaded Return) → www.jwwinco.com

How to order	
1	Length $l$
2	Finish

**GN 425.5-100-NI**

1.1  
1.2  
1.3  
1.4  
2.1  
2.2  
2.3  
2.4