



Metric table

Dimensions in: millimeters - inches

¹ d ₁	² l ₁ ±0.5	l ₂	b	d ₂ Thread	d ₃	h ₁	h ₂	h ₃	h ₄	t min.
10 0.39	120 4.72	94 3.70	16 0.63	M 5	18 0.71	53 2.09	43 1.69	8 0.31	24 0.94	12 0.47
10 0.39	180 7.09	94 3.70	16 0.63	M 5	18 0.71	56 2.20	43 1.69	8 0.31	24 0.94	12 0.47

Specification

- Steel, matte chrome-plated finish
- Grip
Plastic
Technopolymer (Polyamide PA)
 - Glass fiber reinforced
 - Temperature resistant up to 302 °F (150 °C)
 - Black, matte finish
- *Plastic Characteristics* → page QVX
- **RoHS compliant**

Information

EN 425.7 cabinet “U” handles made of steel feature a plastic grip which, owing to its insulating properties, allows it to be used under high surface temperatures.

The above temperature distribution curve has been measured at a surface temperature of 392 °F (200 °C) and a room temperature of 73 °F (23 °C).

see also...

- *Cabinet “U” Handles GN 425 (Steel)* → page QVX

How to order ¹ ² EN 425.7-10-120	1	Handle diameter d ₁
	2	Length l ₁