



SS Stainless Steel

IF product design award

GERMAN DESIGN AWARD

Metric table

Dimensions in: millimeters - inches

¹ d ₁	² d ₂ Thread	² d ₃ H9 Bore	b	d ₄	h ₁	h ₂ ≈	t min.
63 2.48	M 6	B 6	7 0.28	16 0.63	41 1.61	12 0.47	12 0.47
63 2.48	M 8	B 8	7 0.28	16 0.63	41 1.61	12 0.47	16 0.63
80 3.15	M 8	B 8	9 0.35	21 0.83	52 2.05	15 0.59	16 0.63
80 3.15	M 10	B 10	9 0.35	21 0.83	52 2.05	15 0.59	20 0.79
100 3.94	M 10	B 10	11 0.43	25 0.98	65 2.56	19 0.75	20 0.79
100 3.94	M 12	B 12	11 0.43	25 0.98	65 2.56	19 0.75	24 0.95

Specification

Stainless steel AISI 316
 - Matte shot-blasted finish
 - Polished finish

MT
PL

- ISO Fundamental Tolerances → page XYZ
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

T-handles GN 5063 are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces.

The T-handles can also be used in particularly aggressive environments thanks to the materials used.

see also...

- T-Handles GN 5064 (Stainless Steel, Hygienic Design) → page XYZ
- T-Handles GN 563 (Plastic) → page XYZ
- T-Handles Screws GN 563.1 (Plastic) → page XYZ
- T-Handles Screws GN 563.2 (Aluminum) → page XYZ
- Wing Nuts GN 8340 (Stainless Steel) → page XYZ
- Wing Screws GN 8350 (Stainless Steel) → page XYZ

How to order

¹ ² ³
GN 5063-80-M10-MT

- 1** Handle diameter d₁
- 2** Thread d₂ (Bore d₃)
- 3** Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4