

SS Stainless Steel

4 Type (Base)







- E0** Without rubber pad, with 1 slotted hole
- E3** With rubber pad, vulcanized, black, with 1 slotted hole
- G0** Without rubber pad, with 2 slotted holes
- G3** With rubber pad, vulcanized, black, with 2 slotted holes

Inch table

Dimensions in: inches - *millimeters*

¹ d ₁	² d ₂ Thread	³ l ₁ Version S / SK				Version U / UK				³ l ₇ Version X
3.15 80	5/16 x 18	-	-	-	-	-	-	-	-	1.02 26
3.15 80	3/8 x 16	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.14 29
3.15 80	1/2 x 13	2.95 75	3.94 100	4.92 125	5.91 150	-	-	-	-	1.26 32
3.15 80	5/8 x 11	-	-	-	-	2.95 75	3.94 100	4.92 125	5.91 150	1.50 38
3.15 80	3/4 x 10	-	-	-	-	3.94 100	4.92 125	5.91 150	-	1.77 45

d ₁	d ₂ Thread	d ₃	d ₄	h ₁	h ₂	h ₃	h ₄	h ₆	l ₈	A/F ₁	A/F ₂	A/F ₃	A/F ₇	m ₁	m ₂	m ₃	r	t
3.15 80	5/16 x 18	0.51 13	0.41 10.5	0.12 3	0.05 1.3	0.47 12	-	0.12 3	2.76 70	-	-	-	1/2	1.06 27	1.02 26	1.97 50	0.59 15	0.31 8
3.15 80	3/8 x 16	0.51 13	0.41 10.5	0.12 3	0.05 1.3	0.47 12	-	0.12 3	2.76 70	11/16	-	-	1/2	1.06 27	1.02 26	1.97 50	0.59 15	0.39 10
3.15 80	1/2 x 13	0.51 13	0.41 10.5	0.12 3	0.05 1.3	0.47 12	-	0.12 3	2.76 70	11/16	-	-	5/8	1.06 27	1.02 26	1.97 50	0.59 15	0.47 12
3.15 80	5/8 x 11	0.51 13	0.41 10.5	0.12 3	0.05 1.3	-	0.71 18	0.12 3	2.76 70	-	1/2	5/16	7/8	1.06 27	1.02 26	1.97 50	0.59 15	0.63 16
3.15 80	3/4 x 10	0.51 13	0.41 10.5	0.12 3	0.05 1.3	-	0.75 19	0.12 3	2.76 70	-	9/16	7/16	1	1.06 27	1.02 26	1.97 50	0.59 15	0.79 20

Stud / socket versions		
 <p>S Without nut SK With nut</p>	 <p>T* Without nut TK* With nut</p>	 <p>U Without nut UK With nut</p>
External hex at the bottom at d_2 3/8 x 16, 1/2 x 13 M 8, M 10, M 12	Wrench flat at the bottom at d_2 - M 16, M 20, M 24	Internal hex at the top, wrench flat at the bottom at d_2 5/8 x 11, 3/4 x 10 M 16, M 20, M 24
 <p>V* Without nut VK* With nut</p>	 <p>W* With adjustable sleeve</p>	 <p>X Tapped socket type</p>
External hex at the top, wrench flat at the bottom at d_2 - M 16	Covered thread, wrench flat at the bottom at d_2 - M 16	External hex with tapped socket at d_2 5/16 x 18, 3/8 x 16, 1/2 x 13, 5/8 x 11, 3/4 x 10 M 8, M 10, M 12, M 16, M 20

* Only available with Metric thread

Metric table

Dimensions in: millimeters - inches

d_1	d_2	l_1		l_2								l_3				l_7				
		Version S / SK		Version T / TK and U / UK								Version V / VK				Version W				Version X
80 3.15	M 8	40 1.57	50 1.97	63 2.48	-	-	-	-	-	-	-	-	-	-	-	-	-	-	26 1.02	
80 3.15	M 10	50 1.97	60 2.36	80 3.15	100 3.94	-	-	-	-	-	-	-	-	-	-	-	-	-	29 1.14	
80 3.15	M 12	60 2.36	80 3.15	100 3.94	125 4.92	-	-	-	-	-	-	-	-	-	-	-	-	-	32 1.26	
80 3.15	M 16	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	75 2.95	100 3.94	125 4.92	150 5.91	110 4.33	135 5.31	160 6.30	185 7.28	38 1.50
80 3.15	M 20	-	-	-	-	75 2.95	100 3.94	125 4.92	150 5.91	200 7.87	250 9.84	-	-	-	-	-	-	-	-	45 1.77
80 3.15	M 24	-	-	-	-	100 3.94	125 4.92	150 5.91	200 7.87	300 11.81	-	-	-	-	-	-	-	-	-	-

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10



d ₁	d ₂ Thread	d ₃	d ₄	d ₅	h ₁	h ₂	h ₃	h ₄	h ₅	h ₆	l ₄	l ₅	l ₆	l ₈
80 3.15	M 8	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	12 0.47	-	-	3 0.12	-	-	-	70 2.76
80 3.15	M 10	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	12 0.47	-	-	3 0.12	-	-	-	70 2.76
80 3.15	M 12	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	12 0.47	-	-	3 0.12	-	-	-	70 2.76
80 3.15	M 16	13 0.51	10.5 0.41	24 0.94	3 0.12	1.3 0.05	-	18 0.71	15 0.59	3 0.12	45 1.77	45 1.77	29 1.14	70 2.76
80 3.15	M 20	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	-	19 0.75	-	3 0.12	-	-	-	70 2.76
80 3.15	M 24	13 0.51	10.5 0.41	-	3 0.12	1.3 0.05	-	22 0.87	-	3 0.12	-	-	-	70 2.76

d ₁	d ₂ Thread	A/F ₁	A/F ₂	A/F ₃	A/F ₄	A/F ₅	A/F ₆	A/F ₇	m ₁	m ₂	m ₃	r	t
80 3.15	M 8	17 0.67	-	-	-	-	-	14 0.55	27 1.06	26 1.02	50 1.97	15 0.59	8 0.31
80 3.15	M 10	17 0.67	-	-	-	-	-	14 0.55	27 1.06	26 1.02	50 1.97	15 0.59	10 0.39
80 3.15	M 12	17 0.67	-	-	-	-	-	17 0.67	27 1.06	26 1.02	50 1.97	15 0.59	12 0.47
80 3.15	M 16	-	12 0.47	8 0.31	10 0.39	12 0.47	20 0.79	22 0.87	27 1.06	26 1.02	50 1.97	15 0.59	16 0.63
80 3.15	M 20	-	15 0.59	10 0.39	-	-	-	27 1.06	27 1.06	26 1.02	50 1.97	15 0.59	20 0.79
80 3.15	M 24	-	19 0.75	12 0.47	-	-	-	-	27 1.06	26 1.02	50 1.97	15 0.59	-

Specification

- Base
Stainless steel AISI 304
Plain, tumbled finish
- Threaded stud / tapped socket
Stainless steel AISI 303
- Inch size hex nut ANSI / ASME B18.2.2
Stainless steel AISI 304
- Metric size hex nut ISO 4032
Stainless steel AISI 304
- Rubber pad
NBR (Perbunan®) 70 ±5 shore A
- Vulcanized, non-skid
- Black
- [Load Rating Information](#) → page 2121
- [Plastic Characteristics](#) → page 2135
- [Stainless Steel Characteristics](#) → page 2143
- [RoHS compliant](#)

Information

GN 43 leveling feet are intended for use in aggressive environments. The wide range of possible combinations of the base and the stud / socket versions make these leveling feet universally applicable. The leveling feet can be screwed to the mounting surface using the slotted mounting hole, which prevents lateral slippage. The types with rubber pad also protect sensitive surfaces.

These leveling feet are supplied fully assembled and cannot be disassembled.

see also...

- [Leveling Feet GN 40 \(Steel, without Mounting Hole\)](#) → page 1516
- [Leveling Feet GN 42 \(Steel, with Mounting Hole\)](#) → page 1526
- [Leveling Feet GN 42 \(Steel, with Slotted Mounting Hole, Rectangular Shape\)](#) → page 1526
- [Leveling Feet GN 41 \(Stainless Steel AISI 304, without Mounting Hole\)](#) → page 1520
- [Leveling Feet GN 43 \(Stainless Steel AISI 304, with Mounting Hole\)](#) → page 1532
- [Leveling Feet GN 44 / GN 45 \(Stainless Steel AISI 316, with / without Mounting Hole\)](#) → page 1524 / 1540
- [Threaded Tube Ends EN 448 \(Plastic\)](#) → page 1578 / 1578
- [Threaded Tube Inserts GN 992.5 \(Stainless Steel\)](#) → page 1581

How to order (Inch)



GN 43-80-3/8X16-75-E0-S

- | | |
|---|--|
| 1 | Base diameter d ₁ |
| 2 | Thread d ₂ |
| 3 | Length l ₁ (Length l ₇) |
| 4 | Type (Base) |
| 5 | Stud / socket version |

How to order (Metric)



GN 43-80-M16-100-G3-UK

- | | |
|---|--|
| 1 | Base diameter d ₁ |
| 2 | Thread d ₂ |
| 3 | Length l ₁ (Length l ₂ , l ₃ , l ₇) |
| 4 | Type (Base) |
| 5 | Stud / socket version |