



Bore for socket cap screw
ISO 4762

Application examples





Metric



SS

Stainless Steel

4

Type

R With cover cap, non-slip

Metric table

Dimensions in: millimeters / inches							
1 d₁	2 h₁	3 d₂	d₃ Through hole for screw	h₂	h₃	t min.	Static load capacity
16 0.63	16 0.63	M 4	M 3	11 0.43	4 0.16	8 0.31	0.25 kN 56.20 lbf
16 0.63	24 0.94	M 4	M 3	19 0.75	4 0.16	8 0.31	0.25 kN 56.20 lbf
20 0.79	20 0.79	M 5	M 4	14 0.55	4 0.16	10 0.39	0.4 kN 89.92 lbf
20 0.79	30 1.18	M 5	M 4	24 0.94	4 0.16	10 0.39	0.4 kN 89.92 lbf
25 0.98	25 0.98	M 6	M 5	17 0.67	4.7 0.19	12 0.47	0.7 kN 157 lbf
25 0.98	40 1.57	M 6	M 5	32 1.26	4.7 0.19	12 0.47	0.7 kN 157 lbf
32 1.26	32 1.26	M 8	M 6	23 0.91	5.7 0.22	16 0.63	1.6 kN 360 lbf
32 1.26	50 1.97	M 8	M 6	41 1.61	5.7 0.22	16 0.63	1.6 kN 360 lbf

Specification		5	6
Base body			
• Aluminum	AL	S	M
• Turned, Anodized finish, black			
• Stainless steel AISL 316L	A4		
• Turned			
Cover cap			
Thermoplastic elastomer (TPE)			
• Hardness ≈ 75 Shore A			
• Black			
RoHS			
On request			
• d ₁ = 25 / 32 in stainless steel with ESD cover cap			
Technical Information		Page	
Plastic Characteristics		QVX	
Stainless Steel Characteristics		QVX	

Equipment feet GN 440 are used to set up devices, smaller machines, or fixtures on worktops or tables. The non-slip cover cap increases stability, reduces wear on the underlying surface and covers the mounting hole from below.

They can be installed either from above using the internal thread d₂ or with a socket cap screw ISO 4762 from below using the through hole d₃. The cover cap is packaged separately and reusable.

The black version ALS offers a discreet appearance and reduces surface reflections. The version A4M is particularly suitable for use in aggressive environments.

see also...	Page
GN 338 Disks with Cover Cap (Steel, with Rubber / Plastic Cap)	QVX
GN 339 Leveling Feet (Steel / Stainless Steel, with Rubber / Plastic Cover Cap)	QVX
GN 438 Rubber Spacer Disks (Steel, with Vulcanized Rubber Pad)	QVX
GN 438.5 Rubber Spacer Disks (Stainless Steel, with Vulcanized Rubber Pad)	QVX
GN 439 Vibration Damping Leveling Feet (Steel, with Vulcanized Rubber Pad)	QVX
GN 439.5 Vibration Damping Leveling Feet (Stainless Steel, with Vulcanized Rubber Pad)	QVX

How to order	
1	Diameter d ₁
2	Length h ₁
3	Thread d ₂
4	Type
5	Material
6	Finish
GN 440-20-30-M5-R-AL S	

www.jwwinco.com | 1-800-877-8351

 WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov

2665