

Specification



- Mounting clamp
Aluminum
- Socket cap screws DIN 912
Stainless steel AISI 304

MT
ELS

- Matte, tumbled finish
- Black anodized finish
- *ISO Fundamental Tolerances* → page 2129
- *Stainless Steel Characteristics* → page 2143
- [RoHS compliant](#)

Accessory

- Adjustable lever kits GN 511 → page 1829

Information

In the standard version, the clamping screw is a DIN 912 socket cap screw with hexagonal socket. It can be replaced by a GN 511 adjustable lever kit (part number, see dimensional table).

see also...

- *Rods / Tubes GN 480.1* → page 1838
- *Swivel Clamp Connector Joints GN 490* → page 1814
- *Two-Way Connector Clamps GN 131* → page 1770


How to order

GN 474.1-B12-B12-ELS

1	Bore d_1
2	Bore d_2
3	Finish

Metric table

Dimensions in: millimeters - inches

1 d ₁ Bore for shaft tolerance h11	2 d ₂ Bore for shaft tolerance h11	d ₃ Clamping thread	k	l ₁	l ₂	m	s ₁ Square	s ₂ Square	Adjustable lever kit for d ₃ 
B 8	B 8	M 4	14 <i>0.55</i>	38 <i>1.50</i>	7 <i>0.28</i>	24 <i>0.94</i>	-	-	GN 511-M4-14
B 10	B 8	M 5	16 <i>0.63</i>	44 <i>1.73</i>	8 <i>0.31</i>	28 <i>1.10</i>	8 <i>0.31</i>	-	GN 511-M5-16
B 10	B 10	M 5	16 <i>0.63</i>	44 <i>1.73</i>	8 <i>0.31</i>	28 <i>1.10</i>	8 <i>0.31</i>	8 <i>0.31</i>	GN 511-M5-16
B 12	B 8	M 5	16 <i>0.63</i>	45 <i>1.77</i>	8 <i>0.31</i>	29 <i>1.14</i>	10 <i>0.39</i>	-	GN 511-M5-16
B 12	B 10	M 5	16 <i>0.63</i>	45 <i>1.77</i>	8 <i>0.31</i>	29 <i>1.14</i>	10 <i>0.39</i>	10 <i>0.39</i>	GN 511-M5-16
B 12	B 12	M 5	16 <i>0.63</i>	45 <i>1.77</i>	8 <i>0.31</i>	29 <i>1.14</i>	10 <i>0.39</i>	10 <i>0.39</i>	GN 511-M5-16
B 15	B 10	M 6	20 <i>0.79</i>	55 <i>2.17</i>	10 <i>0.39</i>	35 <i>1.38</i>	12 <i>0.47</i>	8 <i>0.31</i>	GN 511-M6-20
B 15	B 12	M 6	20 <i>0.79</i>	55 <i>2.17</i>	10 <i>0.39</i>	35 <i>1.38</i>	12 <i>0.47</i>	10 <i>0.39</i>	GN 511-M6-20
B 15	B 15	M 6	20 <i>0.79</i>	55 <i>2.17</i>	10 <i>0.39</i>	35 <i>1.38</i>	12 <i>0.47</i>	12 <i>0.47</i>	GN 511-M6-20
B 16	B 10	M 6	20 <i>0.79</i>	55 <i>2.17</i>	10 <i>0.39</i>	35 <i>1.38</i>	-	8 <i>0.31</i>	GN 511-M6-20
B 16	B 12	M 6	20 <i>0.79</i>	55 <i>2.17</i>	10 <i>0.39</i>	35 <i>1.38</i>	-	10 <i>0.39</i>	GN 511-M6-20
B 16	B 15	M 6	20 <i>0.79</i>	55 <i>2.17</i>	10 <i>0.39</i>	35 <i>1.38</i>	-	12 <i>0.47</i>	GN 511-M6-20
B 16	B 16	M 6	20 <i>0.79</i>	55 <i>2.17</i>	10 <i>0.39</i>	35 <i>1.38</i>	-	-	GN 511-M6-20
B 20	B 12	M 6	25 <i>0.98</i>	66 <i>2.60</i>	12.5 <i>0.49</i>	41 <i>1.61</i>	16 <i>0.63</i>	12 <i>0.47</i>	GN 511-M6-25
B 20	B 15	M 6	25 <i>0.98</i>	66 <i>2.60</i>	12.5 <i>0.49</i>	41 <i>1.61</i>	16 <i>0.63</i>	12 <i>0.47</i>	GN 511-M6-25
B 20	B 16	M 6	25 <i>0.98</i>	66 <i>2.60</i>	12.5 <i>0.49</i>	41 <i>1.61</i>	16 <i>0.63</i>	-	GN 511-M6-25
B 20	B 20	M 6	25 <i>0.98</i>	66 <i>2.60</i>	12.5 <i>0.49</i>	41 <i>1.61</i>	16 <i>0.63</i>	16 <i>0.63</i>	GN 511-M6-25

3.1
3.2
3.3
3.4
3.5
3.6
3.7
3.8
3.9
3.10

