



SS Stainless Steel

Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂		2 d ₂		3 Length l						d ₃	h	k
	EN 529		EN 529.5										
15 0.59	M 3	M 4	M 3	M 4	6 0.24	10 0.39	16 0.63	-	-	-	11 0.43	11 0.43	9 0.35
15 0.59	M 5	-	M 5	-	10 0.39	16 0.63	25 0.98	-	-	-	11 0.43	11 0.43	9 0.35
18 0.71	M 5	-	M 5	-	10 0.39	16 0.63	25 0.98	40*	-	-	13 0.51	12 0.47	9 0.35
22 0.87	M 6	-	M 6	-	10 0.39	16 0.63	20 0.79	25 0.98	30 1.18	40*	15 0.59	14 0.55	10 0.39
25 0.98	M 6	M 8	M 6	-	16 0.63	25 0.98	-	-	-	-	19 0.75	18 0.71	12 0.47
30 1.18	M 8	-	M 8	-	16 0.63	25 0.98	40 1.57	-	-	-	24 0.94	18 0.71	12 0.47
35 1.38	M 8	-	-	-	25 0.98	40 1.57	-	-	-	-	27 1.06	23 0.91	15 0.59

* These sizes are only available for EN 529

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- **EN 529**
Threaded stud
Steel, zinc plated, blue passivated finish
- **EN 529.5**
Threaded stud
Stainless steel AISI 303
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

The surface quality of EN 529 and EN 529.5 knurled screws is of a sufficiently high standard to meet the highest requirements. Flash marks are not visible.
Duroplast material is highly resistant to chemicals.

How to order (Steel threaded stud) EN 529-25-M8-16	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l
How to order (Stainless steel threaded stud) EN 529.5-18-M5-16	1	Handle diameter d ₁
	2	Thread d ₂
	3	Length l

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4