



3 Type

- A With socket cap screw DIN 912
- B With adjustable lever

Metric table

Dimensions in: millimeters - inches

1 d ₁ Clamping Ø	2 d ₂ Clamping Ø	d ₃ Thread	d ₄	l ₁	l ₂	l ₃	l ₄	l ₅	m
8 0.31	8 0.31	M 6	28 1.10	33 1.30	35 1.38	45 1.77	14 0.55	5 0.20	13 0.51
10 0.39	10 0.39	M 8	32 1.26	45 1.77	45 1.77	63 2.48	20 0.79	5 0.20	15 0.59
12 0.47	12 0.47	M 8	36 1.42	47 1.85	45 1.77	63 2.48	21 0.83	5 0.20	17 0.67
14 0.55	14 0.55	M 8	46 1.81	57 2.24	55 2.17	78 3.07	25.5 1.00	6 0.24	20 0.79
15 0.59	15 0.59	M 10	46 1.81	57 2.24	55 2.17	78 3.07	25.5 1.00	6 0.24	21 0.83
16 0.63	16 0.63	M 10	46 1.81	57 2.24	55 2.17	78 3.07	25.5 1.00	6 0.24	22 0.87
18 0.71	18 0.71	M 10	56 2.20	63 2.48	55 2.17	78 3.07	28.5 1.12	6 0.24	24 0.94
20 0.79	20 0.79	M 10	56 2.20	65 2.56	55 2.17	78 3.07	28.5 1.12	8 0.31	28 1.10

Specification

- Body
Aluminum
 - Matte, tumbled finish **MT**
 - Powder coated
Black, RAL 9005, textured finish **SW**
- Body
Stainless steel AISI CF-8 **NI**
 - Precision casting
 - Matte shot-blasted finish
- Socket cap screws DIN 912
Stainless steel AISI 304
- Hex nuts DIN 934
Stainless steel AISI 304
- Adjustable lever
 - Zinc die-cast (for MT / SW)
Powder coated
Silver, RAL 9006, textured finish
 - Stainless steel AISI CF-8 (for NI)
Precision casting
Matte shot-blasted finish
 - Insert / distance bushing
Stainless steel AISI 303
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Information

Swivel clamp connector joints GN 490, clamp rods or tubes via a V-groove, allowing a greater Ø tolerance to be bridged.

The compression spring makes clamping and releasing easier.

see also...

- *Two-Way Mounting Clamps GN 474* → page 1821
- *Twistable Two-Way Mounting Clamps GN 475* → page 1824
- *Base Plate Mounting Clamps GN 473* → page 1819
- *Rods / Tubes GN 480.1* → page 1838

How to order (Aluminum)	1 Clamping diameter d ₁
	2 Clamping diameter d ₂
	3 Type
GN 490-14-14-A-SW	4 Finish

How to order (Stainless steel)	1 Clamping diameter d ₁
	2 Clamping diameter d ₂
	3 Type
GN 490-10-10-A-NI	4 Finish