



Metric



elesa  
Original design CT-FG

SS Stainless Steel

Metric table

1

2

3

Dimensions in: millimeters / inches

| d <sub>1</sub> | d <sub>2</sub> | Length l   |            |            |            |            |            |            |            |                 |            |            |            | d <sub>3</sub> | h <sub>1</sub> | h <sub>2</sub> | s           | t min.    |
|----------------|----------------|------------|------------|------------|------------|------------|------------|------------|------------|-----------------|------------|------------|------------|----------------|----------------|----------------|-------------|-----------|
|                |                | Steel      |            |            |            |            |            |            |            | Stainless steel |            |            |            |                |                |                |             |           |
| 25<br>0.98     | M 5            | 10<br>0.39 | 16<br>0.63 | -          | -          | -          | -          | -          | 10<br>0.39 | 16<br>0.63      | 25<br>0.98 | -          | -          | 13<br>0.51     | 24<br>0.94     | 6<br>0.24      | 6.5<br>0.26 | 6<br>0.24 |
| 30<br>1.18     | M 6            | 10<br>0.39 | 12<br>0.47 | 16<br>0.63 | 20<br>0.79 | 25<br>0.98 | 30<br>1.18 | 40<br>1.57 | 10<br>0.39 | 16<br>0.63      | 20<br>0.79 | 25<br>0.98 | 30<br>1.18 | 15.5<br>0.61   | 28<br>1.10     | 8<br>0.31      | 7<br>0.28   | 8<br>0.31 |
| 30<br>1.18     | M 8            | 16<br>0.63 | 20<br>0.79 | 25<br>0.98 | 30<br>1.18 | 40<br>1.57 | 45<br>1.77 | -          | 16<br>0.63 | 20<br>0.79      | 25<br>0.98 | 30<br>1.18 | -          | 15.5<br>0.61   | 28<br>1.10     | 8<br>0.31      | 7<br>0.28   | 8<br>0.31 |

Specification

Handle

- Plastic, Polyamide (PA)
- Glass fiber reinforced
- Operating temperature -22 °F to +266 °F (-30 °C to +130 °C)
- Black, matte finish

Blind tapped insert

Brass MS

Threaded stud

- Steel ST
- Zinc plated, blue passivated finish
- Stainless steel AISI 303 NI

RoHS

Wing nuts / Wing screws EN 531.5 clamp and fasten parts easily without tools. Their ergonomic shape and protruding collar make them easy to use.

see also...

|                                                                          | Page |
|--------------------------------------------------------------------------|------|
| EN 531.1 Wing Screws (Plastic, Threaded Stud Steel, with Projecting Hub) | QVX  |
| GN 431 Wing Screws (Stainless Steel)                                     | QVX  |
| GN 433 Wing Screws (Stainless Steel)                                     | QVX  |
| EN 532 Wing Nuts (Plastic, Threaded Bushing Brass)                       | QVX  |
| GN 432 Wing Nuts (Stainless Steel)                                       | QVX  |

Technical Information

|                                 |     |
|---------------------------------|-----|
| Plastic Characteristics         | QVX |
| Stainless Steel Characteristics | QVX |

|                                    |                   |                         |
|------------------------------------|-------------------|-------------------------|
| How to order (Blind tapped insert) | 1                 | Diameter d <sub>1</sub> |
|                                    | 2                 | Thread d <sub>2</sub>   |
|                                    | 4                 | Material                |
|                                    | EN 531.5-25-M5-MS |                         |

|                              |                      |                         |
|------------------------------|----------------------|-------------------------|
| How to order (Threaded stud) | 1                    | Diameter d <sub>1</sub> |
|                              | 2                    | Thread d <sub>2</sub>   |
|                              | 3                    | Length l                |
|                              | 4                    | Material                |
|                              | EN 531.5-30-M6-30-NI |                         |