



Metric table

1	2	d ₁	d ₂	b	d ₃	d ₄	d ₅	h ₁	h ₂ ≈	t min.
63 2.48	M 6	7 0.28	16 0.63	16.8 0.66	12 0.47	41 1.61	12 0.47	12 0.47	12 0.47	12 0.47
80 3.15	M 8	9 0.35	21 0.83	21.8 0.86	17 0.67	52 2.05	15 0.59	15 0.59	16 0.63	16 0.63
100 3.94	M 10	11 0.43	25 0.98	25.8 1.02	21 0.83	65 2.56	19 0.75	19 0.75	20 0.79	20 0.79

Specification

- Body
Stainless steel
precision casting AISI 316
 - Matte finish ($R_a < 0.8 \mu\text{m}$) **MT**
 - Polished finish ($R_a < 0.8 \mu\text{m}$) **PL**
- Sealing ring
 - H-NBR
Temperature resistant
 -13°F to $+302^{\circ}\text{F}$ (-25°C to $+150^{\circ}\text{C}$)
 - EPDM
Temperature resistant
 -40°F to $+248^{\circ}\text{F}$ (-40°C to $+120^{\circ}\text{C}$)
 - Blue
 - Hardness 85 ± 5 Shore A
 - FDA compliant
- [Plastic Characteristics](#) → page QVX
- [Stainless Steel Characteristics](#) → page QVX
- RoHS

3 4

Information

T-handles GN 5064 comply with the DGUV testing principles and are intended for use in hygienic areas. The version with PL finish is additionally certified according to the guidelines of the EHEDG. The sealed mounting surface enables mounting without dead spaces; the impervious geometry in combination with the high quality finish prevents the accumulation of dirt and facilitates cleaning.

T-handles are great for lifting, moving and operating parts or for clamping purposes by means of threads. The ergonomic shape allows for high operating forces.

The T-handles can also be used in particularly aggressive environments thanks to the material used.

see also...

- [Product Family Hygienic Design](#) → page QVX
- [T-Handles EN 563 \(Plastic\)](#) → page QVX
- [T-Handles EN 563.1 \(Plastic\)](#) → page QVX
- [T-Handles GN 563.2 \(Aluminum\)](#) → page QVX
- [T-Handles GN 5063 \(Stainless Steel\)](#) → page QVX
- [Wing Nuts GN 8341 \(Stainless Steel, Hygienic Design\)](#) → page QVX

Accessory

- Sealing rings GN 7600 → page QVX

On request

- with FKM sealing ring (Fluorine rubber) **F**

How to order

GN 5064-63-M6-PL-E

1	Handle diameter d ₁
2	Thread d ₂
3	Finish
4	Sealing ring material

