



3 Type

- A Blank type
- C With plain blind bore, tol. H7
- D With tapped through bore
- E With tapped blind bore

Inch table

Dimensions in: inches - millimeters

| 1 d_1 | 2 d_2 Thread Type E | $d_4 + 0.02$ | $h_1 - 0.04$ | $h_2 \approx$ | t_1 min. | t_2 | |
|----------------|------------------------------------|--------------|--------------|---------------|---------------|------------|------------|
| 1.57 40 | 1/4 x 20 | 5/16 x 18 | 0.55 14 | 0.98 25 | 0.49 12.5 | 0.59 15 | 0.51 13 |
| 1.97 50 | 5/16 x 18 | 3/8 x 16 | 0.71 18 | 1.26 32 | 0.63 16 | 0.71 18 | 0.63 16 |
| 2.36 60 | 3/8 x 16 | 1/2 x 13 | 0.79 20 | 1.57 40 | 0.79 20 | 0.87 22 | 0.79 20 |
| 2.76 70 | 1/2 x 13 | 5/8 x 11 | 0.98 25 | 1.81 46 | 0.91 23 | 1.10 28 | 0.79 20 |

Metric table

Dimensions in: millimeters - inches

| 1 d_1 | 2 d_2 Thread Type E | 2 d_3 H7 Bore Type C | $d_4 + 0.5$ | $h_1 - 1$ | $h_2 \approx$ | t_1 min. | t_2 | |
|----------------|------------------------------------|-------------------------------------|-------------|------------|--------------------------|---------------|------------|------------|
| | | Type D / Type E | | Type A | Type C / Type D / Type E | | | |
| 40 1.57 | M 6 | M 8 | 14 0.55 | 26 1.02 | 25 0.98 | 12.5 0.49 | 15 0.59 | 13 0.51 |
| 50 1.97 | M 8 | M 10 | 18 0.71 | 33 1.30 | 32 1.26 | 16 0.63 | 18 0.71 | 16 0.63 |
| 60 2.36 | M 10 | M 12 | 20 0.79 | 41 1.61 | 40 1.57 | 20 0.79 | 22 0.87 | 20 0.79 |
| 70 2.76 | M 12 | M 16 | 25 0.98 | 47 1.85 | 46 1.81 | 23 0.91 | 28 1.10 | 20 0.79 |

Specification

- Aluminum
 - Matte, tumbled finish **MT**
 - Flash mark not visible
 - Polished finish **PL**
(only available in Type C, D, E in metric sizes)
- Cross Holes GN 110 → page 2042
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

On request

- Special threads, bores, or threaded studs in matte finish only
- Other modifications such as cross holes and set screw holes

Information

GN 5336 star knobs are forged; therefore, a close grain structure is maintained providing a high tensile strength and a smooth surface. Casting flash is eliminated through high quality production techniques. Original ELESA design, now produced in metal in agreement with ELESA S.p.A.

| | |
|---------------------------|--------------------------------|
| How to order (Blank type) | 1 Handle diameter d_1 |
| GN 5336-50-A-MT | 3 Type |
| | 4 Finish |

| | |
|-------------------------------|--------------------------------|
| How to order (Inch) | 1 Handle diameter d_1 |
| GN 5336-40-1/4X20-E-MT | 2 Thread d_2 |
| | 3 Type |
| | 4 Finish |

| | |
|----------------------------|-------------------------------------|
| How to order (Metric) | 1 Handle diameter d_1 |
| GN 5336-60-B12-C-PL | 2 Bore d_3 (Thread d_2) |
| | 3 Type |
| | 4 Finish |

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4