



**Inch table**

Dimensions in: inches - millimeters

1 d <sub>1</sub>	2 d <sub>2</sub>	3 Length l				d <sub>3</sub>	h <sub>1</sub> +0.04	h <sub>2</sub> +0.04
		0.50	0.75	1.00	-			
1.26 32.0	1/4 x 20	0.50 12.7	0.75 19.1	1.00 25.4	-	0.75 19.1	0.91 23.1	0.43 10.9
1.57 39.9	5/16 x 18	0.75 19.1	1.00 25.4	1.25 31.8	-	0.83 21.1	1.06 26.9	0.47 11.9
1.97 50.0	3/8 x 16	1.00 25.4	1.25 31.8	1.50 38.1	2.00 50.8	0.98 24.9	1.30 33.0	0.55 14.0

**Metric table**

Dimensions in: millimeters - inches

1 d <sub>1</sub>	2 d <sub>2</sub>	3 Length l				d <sub>3</sub>	h <sub>1</sub> +1	h <sub>2</sub> +1
		10	16	20	35			
32 1.26	M 6	10 0.39	16 0.63	20 0.79	35 1.38	19 0.75	23 0.91	11 0.43
40 1.57	M 8	20 0.79	25 0.98	30 1.18	35 1.38	45 1.77	27 1.06	12 0.47
50 1.97	M 10	20 0.79	30 1.18	40 1.57	50 1.97	25 0.98	33 1.30	14 0.55
60 2.36	M 12	30 1.18	40 1.57	50 1.97	-	27 1.06	37 1.46	17 0.67

**Specification**

- Five-lobed knob  
Plastic  
Duroplast (Phenolic PF)  
- Temperature resistant up to 203 °F (110 °C)  
- Black, shiny finish
- Threaded stud  
Stainless steel AISI 303
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

**Information**

EN 5337.5 five-lobed knobs, which offer the fingers a secure grip, are solid, so that there are no cavities where unhealthy residues may be deposited.

The stainless steel insert makes this knob suitable for use on medical machines, equipment for the food and pharmaceutical industry, and wherever hygienic, climatic and environmental factors or laws require the use of corrosion resistant materials.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Solid Five-Lobed Knobs EN 5337.4 (Technopolymer Plastic) → page 608
- Five-Lobed Knobs EN 5337.2 (Technopolymer Plastic) → page 602

**On request**

- Special shorter than listed stud lengths and various stud tips

How to order <b>EN 5337.5-1.97-3/8X16-1.50</b>	1	Handle diameter d <sub>1</sub>
	2	Thread d <sub>2</sub>
	3	Length l