



Metric table

Dimensions in: millimeters - inches

¹ d ₁ +0.5	² d ₂ Thread	d ₃	l ₁	l ₂ min.	l ₃
24 0.94	M 8	20.5 0.81	65 2.56	30 1.18	7 0.28
24 0.94	M 10	20.5 0.81	65 2.56	40 1.57	7 0.28
26 1.02	M 8	21 0.83	80 3.15	40 1.57	7 0.28
26 1.02	M 10	21 0.83	80 3.15	55 2.17	7 0.28
26 1.02	M 12	21 0.83	80 3.15	55 2.17	7 0.28
28 1.10	M 10	22 0.87	90 3.54	56 2.20	7 0.28
28 1.10	M 12	22 0.87	90 3.54	58 2.28	10 0.39

Specification

- Body
Plastic
Technopolymer (Polypropylene PP)
- Softline coating
Elastomer (TPE) 70 shore A
 - Chemically bonded with the plastic body
 - FDA compliant plastic granulate
 - Temperature resistant up to 176 °F (80 °C)
 - Black, matte finish
- [Elastomer Characteristics](#) → page QVX
- [Plastic Characteristics](#) → page QVX
- [RoHS compliant](#)

Information

The Softline coating of EN 519.6 cylindrical handles makes them particularly ergonomic and easy to grip.

The soft, slip-proof contact area improves the grip both in damp (hand perspiration) and in dry ambient conditions, as well as in the event of oily surfaces and in very high or very low temperatures.

see also...

- [Product Family Softline](#) → page QVX
- [Cylindrical Handles EN 519](#) → page QVX
- [Cylindrical Handles EN 519.1 \(Press-On Type\)](#) → page QVX

How to order ¹ ² EN 519.6-24-M8	1	Handle diameter d ₁
	2	Thread d ₂