



2 Bore code
B Without keyway
K With keyway

4 Type
R With revolving handle

Metric table

d ₁	d ₂ H7	d ₃	d ₄	d ₅	b	l ₁	l ₂	l ₃	r	Ø Handle
80 3.15	8 0.31	18 0.71	20.5 0.81	25 0.98	18 0.71	17 0.67	35 1.38	45 1.77	29 1.14	16 0.63
100 3.94	10 0.39	18 0.71	20.5 0.81	25.5 1.00	20 0.79	17 0.67	37 1.46	60 2.36	37 1.46	18 0.71
125 4.92	12 0.47	22 0.87	26 1.02	31 1.22	22 0.87	22 0.87	44 1.73	65 2.56	48 1.89	22 0.87
160 6.30	14 0.55	26 1.02	31 1.22	40 1.57	25 0.98	27 1.06	51 2.01	80 3.15	65 2.56	23 0.91
200 7.87	16 0.63	30 1.18	36 1.42	48.5 1.91	28 1.10	34 1.34	61 2.40	80 3.15	84 3.31	24 0.94

Specification

- Plastic
Special high-impact strength Technopolymer (Polypropylene PP)
- Certified in accordance with FDA
- High strength reinforced, shock-resistant
- Temperature resistant up to 176 °F (80 °C)
- Black, matte finish
- Hub bushing
Stainless steel AISI 304
Molded-in
- Cover
Stainless steel AISI 304
Self-adhesive
- Revolving handles
- Plastic, Technopolymer
Black, matte finish
- Certified in accordance with FDA
- Threaded spindle
Stainless steel AISI 304
- Keyways WN / DIN 6885 → page QVX
- Cross holes GN 110 → page QVX
- ISO Fundamental Tolerances → page QVX
- Plastic Characteristics → page QVX
- Stainless Steel Characteristics → page QVX
- RoHS compliant

Information

EN 522.5 two spoked handwheels have an ergonomically shaped rim for a safer and more comfortable grip.
 Suitable for use in corrosion free environments. Specifically, the FDA certified plastic materials allow the use in the food industry.
 Resistant to solvents, oils, grease and other chemical agents.
 see also...
 • Countersunk Washers GN 184.5 (Stainless Steel, for Axial Fixing) → page QVX

On request

- Other modifications such as special inch and metric bores, set screw holes, etc.

<p>How to order</p> <p>EN 522.5-125-B12-R</p>	1	Handwheel diameter d ₁
	2	Bore code
	3	Bore diameter d ₂
	4	Type