



Metric table

Dimensions in: millimeters - inches

¹ d_1	² d_2 Thread	d_3	l_1	l_2
18 0.71	M 6	15 0.59	40 1.57	16 0.63
21 0.83	M 8	17 0.67	50 1.97	16 0.63
23 0.91	M 10	19 0.75	65 2.56	16 0.63
26 1.02	M 10	21 0.83	80 3.15	16 0.63
28 1.10	M 12	22 0.87	90 3.54	16 0.63
31 1.22	M 12	25 0.98	102 4.02	16 0.63

Specification

- Plastic
Duroplast (Phenolic PF)
- Temperature resistant up to 230 °F (110 °C)
- Black, shiny finish
- Threaded stud
Steel, zinc plated, blue passivated finish
- Plastic Characteristics → page QVX
- RoHS compliant

Information

EN 539 fixed cylindrical handles can equally well be used to replace ball knobs on operating / gear lever handles. In that case the operating end of the lever handle will need to have a tapped hole for mounting the EN 539 fixed cylindrical handle.

The threaded stud is deeply embedded in the handle which greatly increases the strength of the plastic body.

see also...

- Revolving Handles GN 598 → page QVX

How to order ¹ ² EN 539-21-M8	1 Handle diameter d_1
	2 Thread d_2