



**3 Type**

- A Without cover cap
- B With cover cap

**Metric table**

1 d <sub>1</sub>	2 d <sub>2</sub> Thread		2 s H9 Square				d <sub>3</sub>	d <sub>4</sub> -0.5	h <sub>1</sub>	h <sub>2</sub>	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub> +0.5
	M 5	M 6	V 5	V 6	-	-							
32 1.26	M 5	M 6	V 5	V 6	-	-	17 0.67	11 0.43	17 0.67	1 0.04	8 0.31	13.5 0.53	6.5 0.26
40 1.57	M 6	M 8	V 6	-	-	-	17 0.67	13 0.51	17 0.67	1 0.04	10 0.39	14.5 0.57	9.5 0.37
50 1.97	M 8	M 10	V 6	V 7	-	-	19 0.75	16 0.63	20 0.79	1.2 0.05	10 0.39	17.5 0.69	9.5 0.37
63 2.48	M 10	M 12	V 6	V 7	V 8	-	22.5 0.89	20 0.79	21.5 0.85	1.3 0.05	10 0.39	19 0.75	9.5 0.37
74 2.91	M 10	M 12	V 7	V 8	V 9	V 10	26.5 1.04	20 0.79	24.5 0.96	2 0.08	15 0.59	21 0.83	13.5 0.53
95 3.74	M 16	-	V 8	V 10	-	-	32 1.26	18 0.71	29.5 1.16	4.5 0.18	15 0.59	26.5 1.04	13.5 0.53

Dimensions in: millimeters - inches

**Specification**

- Five-lobed knob
  - Plastic
  - Technopolymer (Polyamide PA)
    - Glass fiber reinforced
    - Temperature resistant up to 266 °F (130 °C)
    - Black, matte finish
- Color of the color cap (only Type B)
 

●	-
●	DOR
●	DGR
●	DGB
●	DBL
●	DRT
●	DGN
- Tapped / square insert
  - Brass
- ISO Fundamental Tolerances → page 2129
- Plastic Characteristics → page 2135
- RoHS compliant

**Information**

These EN 5331 knobs are characterized by their 5 lobes and recessed grips. They not only give them an attractive design, but their shape also allows a high torque to be achieved.

How to order (Black cover cap)	1 Handle diameter d <sub>1</sub>
<b>EN 5331-63-M10-A</b>	2 Thread d <sub>2</sub> (Square s)
	3 Type
	4 Color of the cover cap
How to order (Colored cover cap)	1 Handle diameter d <sub>1</sub>
<b>EN 5331-74-M12-B-DRT</b>	2 Thread d <sub>2</sub> (Square s)
	3 Type
	4 Color of the cover cap