



Metric table

| ¹ d ₁ | ² d ₂ | ³ Length l | d ₃ | d ₄ | h ₁ | h ₂ | t min. | |
|-----------------------------|-----------------------------|-----------------------|----------------|----------------|----------------|----------------|------------|------------|
| 50 1.97 | M 10 | 20 0.79 | 50 1.97 | 23 0.91 | 27 1.06 | 84 3.31 | 62 2.44 | 17 0.67 |

Dimensions in: millimeters - inches

Specification

- Six-lobed knob
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish
- Color of the cover cap (shiny finish):
Orange, RAL 2004 ● OR
- Tapped insert
Brass
- Threaded Stud
Steel, zinc plated, blue passivated finish
- *Plastic Characteristics* → page QVX
- RoHS compliant

On request

- Black cover cap

Information

EN 5332 six-lobed knobs are used when circumstances require an extended shaft, particularly when clamping fixture and clamping point are too far apart.
Resistant to solvents, oils, grease and other chemical agents.

| | | |
|---|---|--------------------------------|
| How to order (Tapped insert) ¹ ² EN 5332-50-M10 | 1 | Handle diameter d ₁ |
| | 2 | Thread d ₂ |
| How to order (Threaded stud) ¹ ² ³ EN 5332-50-M10-50 | 1 | Handle diameter d ₁ |
| | 2 | Thread d ₂ |
| | 3 | Length l |