



2 Type

- A Without dipstick
- B With dipstick

Metric table



Dimensions in: millimeters - inches

d ₁ Pipe thread	d ₂	l ₁	l ₂	l ₃
G 1/4	20.5 0.81	9 0.35	19 0.75	192 7.56
G 3/8	25 0.98	9 0.35	21 0.83	192 7.56
G 1/2	28 1.10	11 0.43	25 0.98	189 7.44
G 3/4	34 1.34	12 0.47	27 1.06	188 7.40
G 1	42 1.65	13 0.51	29 1.14	188 7.40
G 1 1/4	52 2.05	13 0.51	32 1.26	185 7.28
G 1 1/2	57 2.24	13 0.51	35 1.38	185 7.28

Specification

- Body
Plastic
Technopolymer (Polyamide PA)
- Black, matte finish
- Temperature resistant up to 212 °F (100 °C)
- Seal
Rubber NBR (Perbunan®)
- Dipstick
Steel, phosphate-treated
- *Elastomer Characteristics* → page 2135
- *Plastic Characteristics* → page 2135
- **RoHS compliant**

On request

- Fluid level markings / special lengths
see GN 109 → page 2045

Information

For thread sizes G 1/2 and larger, the seal of EN 548.1 fluid fill plugs is embedded in a radial recess, and thus cannot be lost or squeezed out during tightening.

MIN-MAX markings can easily be applied on the flat sides of the dipstick (see GN 109 → page 2045).

see also...

- *Threaded Plugs GN 441 / GN 442 (with Finger Grip)* → page 1684

<p>How to order</p> <p>EN 548.1-G1/2-B</p>	1	Pipe thread d ₁
	2	Type