




Metric table

Dimensions in: millimeters / inches						
d ₁	d ₂	d ₅	d ₆	h ₁	h ₂	t ₁
25 0.98	M 5	13 0.51	8 0.31	19 0.75	8 0.31	10 0.39
32 1.26	M 6	15 0.59	10 0.39	23 0.91	10 0.39	12 0.47
40 1.57	M 8	17 0.67	13 0.51	27 1.06	12 0.47	18 0.71
50 1.97	M 10	19 0.75	15 0.59	32 1.26	14 0.55	20 0.79

Specification

Knob

Plastic, Polyamide (PA)

- Reinforced, shock resistant
- Self-extinguishing
- Operating temperature
-22 °F to +302 °F (-30 °C to +150 °C)
- Black, matte finish

SV

Tapped insert

Brass

Cover cap for d₁ = 32...50

Plastic, Polyamide (PA)

Black, RAL 9005, matte finish

RoHS

On request

- Cover caps in other colors
- Inch sizes

Five-lobed knobs EN 5337.2 Type SV are produced from a plastic material, which according to UL 94 V-O is classified as a self-extinguishing material. This classification to UL 94 V-O (Underwriters Laboratories) determines the resistance of a plastic material to fire. This comprises a test on a piece of plastic material of a specific form and dimensions in a vertical position to be set afire, whereby the flame according to V-O must extinguish itself without burning droplets developing.

see also...

	Page
EN 5337.2 Five-Lobed Knobs (with Brass / Steel Insert)	QVX
EN 5337 Solid Five-Lobed Knobs (Phenolic Resin)	QVX
EN 5337.4 Solid Five-Lobed Knobs (with Stainless Steel / Brass Tapped Insert)	QVX
EN 5337.6 Five-Lobed Knobs (Softline)	QVX
EN 5337.2 Five-Lobed Knobs (Steel Threaded Stud)	QVX

Technical Information

Plastic Characteristics

QVX