



Application example



Load capacity



5 Type

- A 2 x slotted holes b<sub>2</sub>, without guide steps
- B 2 x bores d, with guide steps
- C 1 x slotted hole b<sub>2</sub>, without guide steps, 1 x bore d, with guide steps

6 Identification no.

- 1 Without cover cap
- 2 With cover cap

Universal table

1	2	3	4	b <sub>1</sub>	n	s <sub>1</sub>	s <sub>2</sub>	b <sub>2</sub>	b <sub>3</sub>	d	h min.	l <sub>1</sub>	l <sub>2</sub>	l <sub>3</sub>	s <sub>3</sub>	Load capacity M in Nm max.	Tightening torque in Nm min.
19	8	40	40	8.5	15	8.5	4	14.5	13	22.5	7	25	5				
0.75	0.31	1.57	1.57	0.33	0.59	0.33	0.16	0.57	0.51	0.89	0.28						
25	8	40	40	8.5	20	8.5	4	14.5	13	22.5	7	30	5				
0.98	0.31	1.57	1.57	0.33	0.79	0.33	0.16	0.57	0.51	0.89	0.28						
43*	-	43	43	8.5	36	-	-	17	13	-	8	35	5				
1.69		1.69	1.69	0.33	1.42			0.67	0.51		0.31						

Dimensions in: millimeters - inches

\* Only available in type A

Specification

- Angle bracket  
Plastic  
Technopolymer (Polyamide PA)  
- Glass fiber reinforced  
- Temperature resistant up to 212 °F (100 °C)  
- Gray, RAL 7046, matte finish
- Cover cap  
Plastic  
Technopolymer (Polyester PBT)  
Gray, similar to RAL 7046, matte finish
- Plastic Characteristics → page QVX
- RoHS compliant

Information

In order to be able to utilize the adjustment range of the types with slotted hole for EN 561 mounting angle brackets, it is recommended to use mounting screws with a low head, e.g. DIN 6912 socket cap screws or ISO 7380 socket button head screws.

EN 561 mounting angle brackets are components designed for universal use.

How to order (Type A)	
1	Width b <sub>1</sub>
3	Length s <sub>1</sub>
4	Length s <sub>2</sub>
5	Type
6	Identification no.
<b>EN 561-25-40-40-A-1</b>	

How to order (Type B / type C)	
1	Width b <sub>1</sub>
2	Slot width n
3	Length s <sub>1</sub>
4	Length s <sub>2</sub>
5	Type
6	Identification no.
<b>EN 561-19-8-40-40-B-2</b>	

3.1  
3.2  
3.3  
3.4  
3.5  
3.6  
3.7  
3.8  
3.9  
3.10