Five-Lobed Knobs

Plastic, with Steel Threaded Stud, Softline





Inch | Metric

elesa
Original design VCT-p.SOFT

SOFT FDA

Inch table

Dimensions in: inches / millimeters

1 d_1	2 d_2	3 Length l	d_3	h_1	h_2
1.69 42.9	5/16 x 18	1.00 25.4	0.67 17	1.14 29	0.43 10.9
2.09 53.1	3/8 x 16	1.50 38.1	0.75 19.1	1.34 34	0.51 13

Metric table

Dimensions in: millimeters / inches

1 d_1	2 d_2	3 Length l				d_3	h_1	h_2
43 1.69	M 6	16 0.63	20 0.79	25 0.98	30 1.18	17 0.67	29 1.14	11 0.43
43 1.69	M 8	16 0.63	20 0.79	25 0.98	30 1.18	17 0.67	29 1.14	11 0.43
53 2.09	M 8	16 0.63	20 0.79	30 1.18	40 1.57	19 0.75	34 1.34	13 0.51
53 2.09	M 10	20 0.79	30 1.18	40 1.57	50 1.97	19 0.75	34 1.34	13 0.51
66 2.60	M 10	20 0.79	30 1.18	40 1.57	50 1.97	21.5 0.85	38.5 1.52	15.5 0.61
66 2.60	M 12	30 1.18	40 1.57	50 1.97	-	21.5 0.85	38.5 1.52	15.5 0.61
77 3.03	M 12	30 1.18	40 1.57	50 1.97	-	26 1.02	46 1.81	21 0.83

Specification

Five-lobed knob
Plastic, Polypropylene (PP)
- Softline coating
  Thermoplastic elastomer (TPE)
  - Chemically bonded with the plastic core
  - FDA compliant plastic granulate
  - Black, matte finish
  - Hardness 70 Shore A

Threaded stud
Steel, zinc plated, blue passivated finish

Cover cap
Plastic, Polypropylene (PP)
Black, RAL 9005, matte finish

Operating temperature
+32 °F to 176 °F (0 °C to +80 °C)

RoHS

On request

- Cover caps in other colors

The Softline coating makes the five-lobed knobs GN 5337.6 particularly user-friendly and ergonomic.
The soft, slip-proof contact area improves the contact both in hot (hand perspiration) and in dry ambient conditions, in the event of oily surfaces and even high or low temperatures.
The use of five-lobed knobs with threaded stud is recommended parvticularly when heavy duty clamping is required.

see also...	Page
EN 5337.6 Five-Lobed Knobs (Softline)	QVX

Technical Information

Product Family Softline	QVX
Plastic Characteristics	QVX

How to order

1 2 3 4
EN 5337.6-1.69-5/16x18-1.00-DSW

1	Handle diameter d_1
2	Thread d_2
3	Length l
4	Cover cap

How to order

1 2 3 4
EN 5337.6-53-M10-30-DSW

1	Handle diameter d_1
2	Thread d_2
3	Length l
4	Cover cap

⚠ WARNING: Cancer and Reproductive Harm — www.P65Warnings.ca.gov