



Metric table

Dimensions in: millimeters - inches

1 d ₁	2 d ₂ Thread	3 Length l				d ₃	d ₄	h ₁	h ₂ ≈
		10	16	20	25				
25* 0.98	M 5	0.39	0.63	0.79	0.98	13 0.51	8 0.31	19 0.75	8 0.31
32 1.26	M 6	0.63	0.79	0.98	1.18	15 0.59	10 0.39	23 0.91	10 0.39
40 1.57	M 8	0.79	0.98	1.18	1.57	17 0.67	13 0.51	27 1.06	12 0.47
50 1.97	M 10	0.79	1.18	1.57	1.77	19 0.75	15 0.59	32 1.26	14 0.55
63 2.48	M 12	1.18	1.57	1.97	-	22 0.87	19 0.75	37 1.46	16 0.63
74 2.91	M 12	1.18	1.97	-	-	26 1.02	17 0.67	43.5 1.71	22 0.87
84 3.31	M 16	1.18	1.97	2.76	-	28 1.10	17 0.67	44 1.73	21 0.83

*Only available with black cover cap

Specification

- Five-lobed knob
Plastic
Technopolymer (Polypropylene PP)
 - Reinforced, shock-resistant
 - Temperature resistant up to 194 °F (90 °C)
 - Black, matte finish
- Threaded stud
Stainless steel AISI 303
- Color of the cover cap (matte finish)
 - Black, RAL 9005
 - Orange, RAL 2004
 - Gray, RAL 7035
 - Yellow, RAL 1021
 - Blue, RAL 5024
 - Red, RAL 3000
 - Green, RAL 6017
- Plastic Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

- **DSW**
- **DOR**
- **DGR**
- **DGB**
- **DBL**
- **DRT**
- **DGN**

Information

The special type of technopolymer used and the matte finish make these EN 5337.7 five-lobed knobs elegant and “soft” to touch. The operator obtains a strong clamping action without any discomfort due to its ergonomic design: five lobes, blended radius and well proportioned rim height assure a natural, safe and comfortable grip.

Resistant to solvents, oils, grease and other chemical agents.

see also...

- Five-Lobed Knobs EN 5337.2 (Steel Threaded Stud) → page 602
- Solid Five-Lobed Knobs EN 5337.4 (Stainless Steel Threaded Stud) → page 608
- Softline Five-Lobed Knobs EN 5337.6 → page 611
- Five-Lobed Knobs EN 5337.7 with Loss Protection GN 111.7 → page 2046

How to order	
1	Handle diameter d ₁
2	Thread d ₂
3	Length l
4	Color of the cover cap

EN 5337.7-40-M8-25-DGN

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4