



Inch table

Dimensions in: inches - millimeters

Length l	d ₂ Thread	h ₁	h ₂	s Square	t min.
2.17 55	1/4 x 20	1.30 33	0.87 22	0.55 14	0.47 12
2.64 67	5/16 x 18	1.46 37	0.98 25	0.63 16	0.63 16
3.15 80	3/8 x 16	1.61 41	1.02 26	0.79 20	0.63 16

Metric table

Dimensions in: millimeters - inches

Length l	d ₁ H7 Bore diameter	d ₂ Thread	h ₁	h ₂	s Square	t min.
55 2.17	B 6	M 6	M 8 33 1.30	22 0.87	14 0.55	12 0.47
67 2.64	B 8	M 8	- 37 1.46	25 0.98	16 0.63	16 0.63
80 3.15	B 8	M 8	M 10 41 1.61	26 1.02	20 0.79	16 0.63

Specification

- Aluminum
 - Powder coated
 - Black, RAL 9005, textured finish
 - Silver, RAL 9006, textured finish
 - Plain, tumbled finish
 - Flash mark not visible
- ISO Fundamental Tolerances → page 2129
- RoHS compliant

- SW
- SR
- BL

Information

GN 563.2 T-handles can be used as either operating handles or for clamping purposes, providing high clamping force.

T-handles are made by forging and therefore they have a structure with high strength and a smooth surface.

An ELESA original design, produced in metal with permission of ELESA S. p. A.

see also...

- T-Handles EN 563 (Technopolymer Plastic) → page 82

On request

- Inch bores

How to order (Inch)	1 Handle length l
GN563.2-55-1/4X20-BL	2 Thread d ₂
	3 Finish
How to order (Metric)	1 Handle length l
GN563.2-67-B8-SR	2 Bore diameter d ₁ (Thread d ₂)
	3 Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4