



Metric table

Dimensions in: millimeters - inches

b	Length l ±0.25	a	d₁	d₂	h	r	t min.
25 0.98	112 4.41	16 0.63	M 6	10 0.39	50 1.97	5 0.20	10 0.39
25 0.98	128 5.04	16 0.63	M 6	10 0.39	54 2.13	7 0.28	10 0.39
25 0.98	160 6.30	16 0.63	M 6	10 0.39	54 2.13	9 0.35	10 0.39
25 0.98	192 7.56	16 0.63	M 6	10 0.39	54 2.13	9 0.35	10 0.39
35 1.38	160 6.30	25 0.98	M 8	17 0.67	68 2.68	12.5 0.49	12 0.47
35 1.38	192 7.56	25 0.98	M 8	17 0.67	68 2.68	12.5 0.49	12 0.47
35 1.38	300 11.81	25 0.98	M 8	17 0.67	68 2.68	12.5 0.49	12 0.47

Specification

- Sheathing
Thermoplastic polyurethane (TPU)
 - Black, matte textured finish
 - Elastic, 65 ±5 shore A
 - Temperature resistant up to 158 °F (70 °C)
 - Abrasion resistant
 - Insulating
 - Weather-proof
- Handle core
 - Stainless steel AISI 303, round (for size b = 25 mm)
 - Aluminum, elliptical (for size b = 35 mm)
- Load Rating Information → page 2068
- Elastomer Characteristics → page 2135
- Stainless Steel Characteristics → page 2143
- RoHS compliant

Information

The shock absorbing Thermoplastic Polyurethane foam rubber coating of GN 564 cabinet “U” handles prevents injuries to the operator, while its elliptical shape gives it a nice hold.

The stainless steel respectively aluminum core guarantees a high basic strength of the handle.

see also...

- Product Family Softline → page 18
- Cabinet “U” Handles GN 565 (Aluminum) → page 98
- Cabinet “U” Handles EN 725 (Technopolymer Plastic) → page 104

On request

- Various metric size fasteners and kit packaging
- Other colors

<p>How to order</p> <p>GN 564-25-128</p>	1	Handle width b
	2	Length l