



SS Stainless Steel

Inch table

Dimensions in: inches - millimeters

d ₁	d ₂ Black version	d ₃	h ₁	h ₂	t ≈
0.98 25	10 x 32	0.47 12	0.79 20	0.39 10	0.39 10
1.26 32	1/4 x 20	0.55 14	0.91 23	0.45 11.5	0.39 10
1.57 40	5/16 x 18	0.63 16	1.06 27	0.53 13.5	0.51 13
1.97 50	3/8 x 16	0.75 19	1.18 30	0.59 15	0.67 17

Metric table

Dimensions in: millimeters - inches

d ₁	d ₂ Black / white version	d ₃	h ₁	h ₂	t ≈
25 0.98	M 5	12 0.47	20 0.79	10 0.39	10 0.39
32 1.26	M 6	14 0.55	23 0.91	11.5 0.45	10 0.39
40 1.57	M 8	16 0.63	27 1.06	13.5 0.53	13 0.51
50 1.97	M 10	19 0.75	30 1.18	15 0.59	17 0.67
60 2.36	M 12	22.5 0.89	34 1.34	18 0.71	20 0.79

Specification

- Three-lobed knob
Plastic
Technopolymer (Polyamide PA)
- Glass fiber reinforced
- Temperature resistant up to 266 °F (130 °C)
- Black, matte finish

—
○ WS

- Tapped insert
Stainless steel AISI 304
- *Plastic Characteristics* → page 2135
- *Stainless Steel Characteristics* → page 2143
- RoHS compliant

Information

The underside of the EN 5342 three-lobed knobs is not recessed, which meets the requirements of a “hygienic” version.

see also...

- *Solid Five-Lobed Knobs EN 5337.4 (Technopolymer Plastic, with Stainless Steel Insert)* → page 606
- *Solid Five-Lobed Knobs EN 5337.4 with Loss Protection GN 111.7* → page 2046

On request

- Brass insert

How to order (Inch, black version)

EN 5342-40-5/16X18

- 1 Handle diameter d₁
- 2 Thread d₂

How to order (Metric, white version)

EN 5342-40-M8-WS

- 1 Handle diameter d₁
- 2 Thread d₂
- 3 Color

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

