


Metric



elesa
Original design HE.

- 4 Type**
A With reflector
B Without reflector

Metric table

2 d_1	3 d_2 H11 Push-fit Ø	d_3	b min.	l_1	l_2
9 0.35	17 0.669	18 0.71	5 0.20	6.5 0.26	3 0.12
12 0.47	20 0.787	21 0.83	6 0.24	8 0.31	3 0.12
17 0.67	26 1.024	28 1.10	6 0.24	7.5 0.30	3.5 0.14
20 0.79	30 1.181	32 1.26	7 0.28	8 0.31	4 0.16
25 0.98	35 1.378	38 1.50	8 0.31	9 0.35	4 0.16
28 1.10	40 1.575	43 1.69	9 0.35	10 0.39	4.5 0.18
32 1.26	45 1.772	47 1.85	9 0.35	11 0.43	5.5 0.22

Dimensions in: millimeters / inches

Specification

Body
Plastic, Polycarbonat (PC)

- Crystal clear
- High mechanical strength
- Not solvent resistant
- Not alcohol resistant

Reflector for type A

- Aluminum
- White painted
 - With red fluid level mark

O-ring

Acrylonitrile butadiene rubber (NBR)

Operating temperature

-22 °F to 212 °F (-30 °C to +100 °C)

RoHS



NO

No thread is required for mounting the fluid sight glasses EN 542.
The sight glass is recessed, thus protecting the window.

Assembly Instruction

Push in the fluid sight glass manually, then a soft-head hammer can be used to complete the insertion. The bore should be countersunk by 45°, the O-ring should be slightly greased.

see also...

GN 537 Fluid Sight Glasses (without Thread) Page QVX

Technical Information

ISO Fundamental Tolerances QVX

Plastic Characteristics QVX

How to order

EN 542-NO-17-26-A

- | | |
|----------|-------------------------|
| 1 | Material |
| 2 | Diameter d_1 |
| 3 | Push-fit diameter d_2 |
| 4 | Type |