



2 Bore code
B Without keyway
K With keyway

Metric table

Dimensions in: millimeters - inches

Length l	d ₁ H7 Bore	d ₂	h	b P9	t
75 2.95	16 0.63	32 1.26	24 0.94	5 0.20	17.3 0.68
90 3.54	18 0.71	34 1.34	26 1.02	6 0.24	19.7 0.78
110 4.33	20 0.79	36 1.42	30 1.18	6 0.24	21.7 0.85
135 5.31	22 0.87	42 1.65	32 1.26	6 0.24	23.7 0.93
165 6.50	24 0.94	44 1.73	36 1.42	8 0.31	25.7 1.01

Specification

- Crank body
Cast iron (GGG)
- Ground and shot-blasted
- Hub face machined
- Knurled handle
Steel, blackened finish
- Indexing pin
Steel, hardened
- Keyways DIN 6885 Page 2 → page QVX
- ISO Fundamental Tolerances → page QVX
- RoHS compliant

On request

- Other modifications such as inch and special metric bores, keyways, set screw holes, cross holes, etc.

Information

GN 558 indexing crank handles are ideal for positioning and holding the crank, after rotation, in a fixed position via the spring loaded pin in the hand grip.

see also...

- Indexing Mechanisms GN 200 → page QVX
- Indexing Levers GN 215 → page QVX
- Indexing Knobs GN 700 (with Stepless Positioning) → page QVX

<p>How to order</p> <p>GN 558-75-K16</p>	1	Length l
	2	Bore code
	3	Bore d ₁