



Universal table

Dimensions in: millimeters - inches

b	l₁	a	d	h₁	h₂	l₂	r	t
20 0.79	100 3.94	13 0.51	5.4 0.21	49 1.93	13.5 0.53	112 4.41	13 0.51	5.5 0.22
20 0.79	112 4.41	13 0.51	5.4 0.21	49 1.93	13.5 0.53	124 4.88	13 0.51	5.5 0.22
20 0.79	117 4.61	13 0.51	5.4 0.21	49 1.93	13.5 0.53	129 5.08	13 0.51	5.5 0.22
20 0.79	120 4.72	13 0.51	5.4 0.21	51 2.01	13.5 0.53	132 5.20	13 0.51	5.5 0.22
20 0.79	128 5.04	13 0.51	5.4 0.21	51 2.01	13.5 0.53	140 5.51	13 0.51	5.5 0.22
20 0.79	160 6.30	13 0.51	5.4 0.21	51 2.01	13.5 0.53	172 6.77	13 0.51	5.5 0.22
26 1.02	116 4.57	17 0.67	6.4 0.25	55 2.17	11 0.43	130 5.12	17 0.67	6 0.24
26 1.02	120 4.72	17 0.67	6.4 0.25	55 2.17	11 0.43	134 5.28	17 0.67	6 0.24
26 1.02	132 5.20	17 0.67	6.4 0.25	55 2.17	11 0.43	146 5.75	17 0.67	6 0.24
26 1.02	164 6.46	17 0.67	6.4 0.25	57 2.24	11 0.43	178 7.01	17 0.67	6 0.24
26 1.02	179 7.05	17 0.67	6.4 0.25	57 2.24	11 0.43	193 7.60	17 0.67	6 0.24
26 1.02	196 7.72	17 0.67	6.4 0.25	57 2.24	11 0.43	210 8.27	17 0.67	6 0.24

Specification

- Body
Aluminum
- Powder coated
 - Black, RAL 9005, textured finish, **SW**
 - Red, RAL 3000, textured finish **RS**
 - Silver, RAL 9006, textured finish **SR**
- Anodized finish, natural color **EL**
- Plain, tumbled finish **BL**
- Mounting holes
Counterbored for inch or metric socket cap screws
- Load Rating Information → page 2068
- RoHS compliant

Information

GN 565.1 cabinet “U” handles are manufactured from a bent aluminum profile and have excellent stability and ergonomic design.

In addition to the standard finishes, these cabinet “U” handles are also available with a functional coating: The **SW** version is coated with a highly weather-resistant and UV-resistant powder coating system, making this version excellent for outdoor use.

see also...

- Cabinet U-Handles GN 565.5 (Stainless Steel, Mounting from the back or the operator's side) → page QVX

On request

- Various metric and inch size fasteners and kit packaging

How to order GN565.1-26-132-SW	1	Handle width b
	2	Length l ₁
	3	Finish

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4