

SS Stainless Steel

4 Type

- A** Mounting from the back (tapped blind hole)
- B** Mounting from the operator's side

Specification

- Stainless steel AISI 304
- Matte shot-blasted finish **GS**
- Slip polished, shiny metallic finish **GP**
(only Type A in metric sizes)
- *Load Rating Information* → page 2068
- *Stainless Steel Characteristics* → page 2143
- **RoHS compliant**

Accessory

- GN 181 Mounting Plate Sets
(Mounting from the Operator's Side) → page XYZ

On request

- Polished version GP in inch sizes
- Various inch and metric size fasteners and kit packaging

Information


GN 565.5 cabinet U-handles are often used in the food industry or other such applications where a non-corrosive material is necessary. The shape of this sturdy handle has good ergonomic features.

These cabinet U-handles are manufactured from a bent aluminum profile.

see also...

- *Cabinet U-Handles GN 565 (Aluminum)* → page 98
- *Cabinet U-Handles GN 565.1 (Aluminum)* → page QVX
- *Cabinet U-Handles GN 426.5 (Stainless Steel)* → page 147
- *Cabinet U-Handles GN 425 (Stainless Steel)* → page 138
- *"Economical" Cabinet U-Handles GN 728.5 (Stainless Steel, Mounting from the Back or from the Operator's Side)* → page 120

How to order (Inch)	1 Handle width b
	2 Thread d ₁
	3 Length l
	4 Type
	5 Finish
 GN 565.5-20-1/4X20-112-A-GS	

How to order (Metric)	1 Handle width b
	2 Thread d ₁ (Bore d ₂)
	3 Length l
	4 Type
	5 Finish
 GN 565.5-20-M6-160-A-GP	

Inch table

Dimensions in: inches - *millimeters*

b	d₁ Thread	Length l Type A Shot-blasted GS	a	h₁	h₂	r	t₁ min.	t₂
0.79 20	1/4 x 20	4.41 112	0.51 13	1.93 49	0.53 13.5	0.51 13	0.39 10	0.22 5.5
0.79 20	1/4 x 20	5.04 128	0.51 13	2.01 51	0.53 13.5	0.51 13	0.39 10	0.22 5.5
0.79 20	1/4 x 20	6.30 160	0.51 13	2.01 51	0.53 13.5	0.51 13	0.39 10	0.22 5.5

Metric table

Dimensions in: millimeters - *inches*

b	d₁ Thread	d₂ Bore	Length l			a	h₁	h₂	r	t₁ min.	t₂
			Type A Shot-blasted GS	Type A Slip polished GP	Type B Shot-blasted GS						
20 0.79	M 6	5.4 0.21	112 4.41	112 4.41	112 4.41	13 0.51	49 1.93	13.5 0.53	13 0.51	10 0.39	5.5 0.22
20 0.79	M 6	5.4 0.21	128 5.04	128 5.04	128 5.04	13 0.51	51 2.01	13.5 0.53	13 0.51	10 0.39	5.5 0.22
20 0.79	M 6	5.4 0.21	160 6.30	160 6.30	160 6.30	13 0.51	51 2.01	13.5 0.53	13 0.51	10 0.39	5.5 0.22
20 0.79	M 6	-	200 7.87	200 7.87	-	13 0.51	51 2.01	-	13 0.51	10 0.39	-
20 0.79	M 6	-	250 9.84	-	-	13 0.51	51 2.01	-	13 0.51	10 0.39	-
20 0.79	M 6	-	300 11.81	-	-	13 0.51	51 2.01	-	13 0.51	10 0.39	-
20 0.79	M 6	-	400 15.75	-	-	13 0.51	51 2.01	-	13 0.51	10 0.39	-
26 1.02	M 8	6.4 0.25	128 5.04	128 5.04	128 5.04	17 0.67	57 2.24	11 0.43	19 0.75	12 0.47	6 0.24
26 1.02	M 8	6.4 0.25	160 6.30	160 6.30	160 6.30	17 0.67	57 2.24	11 0.43	19 0.75	12 0.47	6 0.24
26 1.02	M 8	6.4 0.25	200 7.87	200 7.87	200 7.87	17 0.67	57 2.24	11 0.43	19 0.75	12 0.47	6 0.24
26 1.02	M 8	-	300 11.81	-	-	17 0.67	57 2.24	-	19 0.75	12 0.47	-
26 1.02	M 8	-	400 15.75	-	-	17 0.67	57 2.24	-	19 0.75	12 0.47	-
26 1.02	M 8	-	500 19.69	-	-	17 0.67	57 2.24	-	19 0.75	12 0.47	-

1.1
1.2
1.3
1.4
2.1
2.2
2.3
2.4

